

Sales Outline Drawing**Revision****A****Specifications:**

Oscillation Frequency (Hz)	300 ~ 500
Operating Voltage (Vdc)	8 ~ 14
Rated Voltage (Vdc)	12
Current Consumption (mA/max)	45 at Rated Voltage
Sound Pressure Level (dB/min)	80 at 30cm at Rated Voltage
Tone/Pulse Rate (Hz0)	Constant
Operating Temperature (°C)	-30 ~ +70
Storage Temperature (°C)	-40 ~ +80
Housing	ABS757 plastic resin (Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	17
Options	For other options contact factory

RoHS Compliant

Dimensions: (units: mm)