


Sealed Nickel-Metal Hydride Rechargeable Batteries

Model:NH-B320


Specifications

Nominal Voltage		1.2 Volt
Rated Capacity		32 mAh
Dimensions	Diameter in. (mm)	0.98 (25.0)
	Height in. (mm)	0.30 (7.6)
	Height with solder tabs	0.34 (8.6)
	Weight Approx.	14.5 gm
	Internal Resistance	<1200 mΩ
	Standard Charge (0.1C)	32 mA
	Trickle Charge	(0.03C)~(0.05C)
	Fast Charge ΔV	n/a
Recommended Operating Temperature Range	Std/Trickle Charge	20±5°C
	Fast Charge	20±5°C
	Discharge	20±5°C
	Storage	-20°C to 45°C
Standard Discharge (0.2C) Cut Off Voltage		1.0V per cell
High Rate Discharge (1 C) Cut Off Voltage		1.0V per cell


Dimensions




Charging and Discharging Characteristics




Discharge Cycle Life



Standard Charge




Standard Battery Discharging (0.2C/0.5C/1C)




Standard Battery Discharging (1C/2C/3C)


Please note the following graphs are for High Temperature and High Power batteries. These batteries do not form part of our standard range, but both types are available on request subject to minimum order quantities and delivery times. Please contact us for further details.




High Temp. Battery Charging and Discharging




High Power (10C Discharge) Cycle Life



High Temp. Battery Discharge Cycle Life



High Temp. Battery Trickle Charge



High Power Battery Discharging (3C/5C/10C)

Corporate Headquarters and Domestic Sales

Power-Sonic Corporation • 7550 Panasonic Way • San Diego, CA 92154 • U.S.A

Phone: (619) 661-2020 • Fax: (619) 661.3650

Email Sales: national-sales@power-sonic.com

Email Customer Service: customer-service@power-sonic.com

E-mail Technical Support: technical-support@power-sonic.com

International Sales

Power-Sonic Corporation • P.O. Box 5242 • Redwood City, CA 94063 • U.S.A.

Phone: (650) 364-5001 • Fax: (650) 366-3662

Email Sales: international-sales.com@power-sonic.com

www.power-sonic.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Power-Sonic:

[NH-B320/10 W/TAB](#) [NH-B320/9 W/TAB](#)