

Unsealed 2.8 Housings – Vertical PC Board Headers

Technical Features

No. of Positions:

6–21 Positions

Housing Material:

PA 66 GF13

Material and Finish

Headers:

CuSn4, tin plated
(silver plated on request)

Wire Size Range:

2.5 mm² FLR Max.

Product Group Drawing:


966140

Product Specification:

108-18619-3

Application Specification:

114-18051



Unsealed 2.8 Housings – PCB Headers

No. of Positions	Housing Color*	Part Numbers		
		Mating Right-Angle PCB Header	Package Quantity	Mating Receptacle Housing
		Packed in plastic anti-static tray and corrugated box	—	8-968970-1
				8-968971-1
				8-968972-1
				8-968973-1
				8-968974-1
				8-968975-1
6	Black	966140-5	—	7-968970-1
9		966140-4		7-968971-1
12		966140-3		7-968972-1
15		966140-2		7-968973-1
18		966140-1		7-968974-1
21		966140-6		7-968975-1
		Packed in non anti-static tray and corrugated box	—	6-968970-1
				6-968971-1
				6-968972-1
				6-968973-1
				6-968974-1
				6-968975-1
6	Black	9-966140-5	—	5-968970-1
9		9-966140-4		5-968971-1
12		9-966140-3		5-968972-1
15		9-966140-2		5-968973-1
18		9-966140-1		5-968974-1
21		9-966140-6		5-968975-1

*) Silver plated on request.