



Micro Commercial Components
21201 Itasca Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

DLZ3.6B THRU DLZ39B

Features

- Small Surface Mounting Type.(LLDS)
- High Reliability
- Silicon Epitaxial Planar

**500 mW
Zener Diode
3.725 to 36.275 Volts**

Maximum Ratings

Symbol	Rating	Rating	Unit
P_D	Power dissipation	500	mW
T_J	Junction Temperature	-55 to +150	$^{\circ}\text{C}$
T_{STG}	Storage Temperature Range	-55 to +150	$^{\circ}\text{C}$




Fig.1 Zener characteristics




Fig.2 Derating curve






Fig.3 Zener voltage -
temp.coefficient characteristics

MINIMELF



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.134	.142	3.40	3.60	
B	.008	.016	0.20	0.40	
C	.055	.059	1.40	1.50	

SUGGESTED SOLDER PAD LAYOUT



DLZ3.6B thru DLZ39B



ELECTRICAL CHARACTERISTICS @25°C

Type	ZENER VOLTAGE V _Z VOLTS			Operating Resistance Z _Z (OHMS)		Rising Operating Resistance Z _{ZK} (OHMS)		REVERSE CURRENT I _R (Max) @ V _R	
	Min.	Max.	I _Z (mA)	Max.	I _Z (mA)	Max.	I _Z (mA)	μA	VOLTS
DLZ3.6B	3.600	3.845	20	60	20	1000	1.0	10	1.0
DLZ3.9B	3.89	4.16	20	50	20	1000	1.0	5.0	1.0
DLZ4.3B	4.17	4.43	20	40	20	1000	1.0	5.0	1.0
DLZ4.7B	4.55	4.80	20	25	20	900	1.0	5.0	1.0
DLZ5.1B	4.94	5.20	20	20	20	800	1.0	5.0	1.5
DLZ5.6B	5.45	5.73	20	13	20	500	1.0	5.0	2.5
DLZ6.2B	5.96	6.27	20	10	20	300	1.0	5.0	3.0
DLZ6.8B	6.49	6.83	20	8.0	20	150	0.5	2.0	3.5
DLZ7.5B	7.07	7.45	20	8.0	20	120	0.5	0.5	4.0
DLZ8.2B	7.78	8.19	20	8.0	20	120	0.5	0.5	5.0
DLZ9.1B	8.57	9.01	20	8.0	20	120	0.5	0.5	6.0
DLZ10B	9.41	9.90	20	8.0	20	120	0.5	0.2	7.0
DLZ11B	10.50	11.05	10	10	10	120	0.5	0.2	8.0
DLZ12B	11.44	12.03	10	12	10	110	0.5	0.2	9.0
DLZ13B	12.55	13.21	10	14	10	110	0.5	0.2	10
DLZ15B	13.89	14.62	10	16	10	110	0.5	0.2	11
DLZ16B	15.25	16.04	10	18	10	150	0.5	0.2	12
DLZ18B	16.82	17.70	10	23	10	150	0.5	0.2	13
DLZ20B	18.63	19.59	10	28	10	200	0.5	0.2	15
DLZ22B	20.64	21.71	5.0	30	5.0	200	0.5	0.2	17
DLZ24B	22.61	23.77	5.0	35	5.0	200	0.5	0.2	19
DLZ27B	24.97	26.26	5.0	45	5.0	250	0.5	0.2	21
DLZ30B	27.70	29.13	5.0	55	5.0	250	0.5	0.2	23
DLZ33B	30.32	31.88	5.0	65	5.0	250	0.5	0.2	25
DLZ36B	32.79	34.49	5.0	75	5.0	250	0.5	0.2	27
DLZ39B	35.36	37.19	5.0	85	5.0	250	0.5	0.2	30