



## NYLON HOLE PLUGS

Closes unused chassis holes quickly and economically. Plugs are abrasion and vibration resistant.




**MATERIAL:** Nylon 6/6, Matte Finish, Black

| CAT. NO. | HOLE DIAMETER | PANEL THICKNESS | B            | C           |
|----------|---------------|-----------------|--------------|-------------|
| 8600     | .250 (6.4)    | .062 (1.57)     | .312 (7.9)   | .312 (7.9)  |
| 8601     | .312 (7.9)    | .062 (1.57)     | .375 (9.5)   | .312 (7.9)  |
| 8602     | .375 (9.5)    | .125 (3.2)      | .468 (11.9)  | .406 (10.3) |
| 8603     | .500 (12.7)   | .125 (3.2)      | .578 (14.7)  | .406 (10.3) |
| 8604     | .625 (15.9)   | .125 (3.2)      | .734 (18.6)  | .406 (10.3) |
| 8605     | .750 (19.1)   | .125 (3.2)      | .921 (23.4)  | .406 (10.3) |
| 8606     | .875 (22.2)   | .125 (3.2)      | 1.015 (25.8) | .453 (11.5) |
| 8607     | 1.000 (25.4)  | .125 (3.2)      | 1.203 (30.6) | .453 (11.5) |
| 8608     | 1.125 (28.6)  | .125 (3.2)      | 1.218 (30.9) | .453 (11.5) |
| 8609     | 1.250 (31.8)  | .125 (3.2)      | 1.375 (34.9) | .453 (11.5) |
| 8610     | 1.375 (34.9)  | .125 (3.2)      | 1.500 (38.1) | .453 (11.5) |
| 8611     | 1.500 (38.1)  | .125 (3.2)      | 1.671 (42.4) | .453 (11.5) |

## STEEL HOLE PLUGS

Excellent spring retention. Plugs will cover chassis holes, wiring outlets, access holes or unused openings.




**MATERIAL:** Steel, Nickel Plate


| CAT. NO. | HOLE DIAMETER | PANEL THICKNESS       | A            | B           | C           | PRONGS |
|----------|---------------|-----------------------|--------------|-------------|-------------|--------|
| 7600     | .250 (6.4)    | .031-.062 (.81-1.57)  | .406 (10.3)  | .234 (5.9)  | .062 (1.57) | 6      |
| 7601     | .312 (7.9)    | .047-.078 (1.19-1.98) | .437 (11.1)  | .250 (6.4)  | .062 (1.57) | 6      |
| 7602     | .375 (9.5)    | .047-.062 (1.19-1.57) | .500 (12.7)  | .234 (5.9)  | .062 (1.57) | 6      |
| 7603     | .500 (12.7)   | .031-.062 (.81-1.57)  | .656 (16.7)  | .281 (7.1)  | .078 (1.98) | 8      |
| 7604     | .625 (15.9)   | .062-.093 (1.57-2.36) | .812 (20.6)  | .296 (7.5)  | .078 (1.98) | 8      |
| 7605     | .750 (19.1)   | .062-.093 (1.5-2.36)  | .921 (23.4)  | .296 (7.5)  | .078 (1.98) | 12     |
| 7606     | .875 (22.2)   | .062-.093 (1.57-2.36) | 1.062 (27.0) | .296 (7.5)  | .062 (1.57) | 12     |
| 7607     | 1.000 (25.4)  | .062-.156 (1.57-3.9)  | 1.140 (29.0) | .328 (8.3)  | .093 (2.36) | 12     |
| 7608     | 1.125 (28.6)  | .031-.125 (.79-3.2)   | 1.312 (33.3) | .343 (8.7)  | .093 (2.36) | 12     |
| 7609     | 1.250 (31.8)  | .062-.093 (1.57-2.36) | 1.437 (36.5) | .343 (8.7)  | .093 (2.36) | 12     |
| 7610     | 1.375 (34.9)  | .031-.125 (.79-3.2)   | 1.562 (39.7) | .406 (10.3) | .078 (1.98) | 12     |
| 7611     | 1.500 (38.1)  | .031-.062 (.79-1.57)  | 1.640 (41.7) | .406 (10.3) | .093 (2.36) | 12     |

## NYLON VENT PLUGS

Used to cover chassis holes while allowing air flow for ventilation.



- Snaps into .032 (.81) to .125 (3.2) thick panels.




**MATERIAL:** Nylon 6/6, Matte Finish, Black

| CAT. NO. | HOLE DIAMETER | B            | C           |
|----------|---------------|--------------|-------------|
| 8612     | .875 (22.2)   | 1.015 (25.8) | .453 (11.5) |
| 8613     | 1.000 (25.4)  | 1.218 (30.9) | .453 (11.5) |

## NYLON SPLIT BUSHINGS

Designed to be assembled into holes that already contain wire or cable. Versatile bushing can be used on all chassis from .032 (.81) to .125 (3.2).





**MATERIAL:** Nylon 6/6, Black

| CAT. NO. | HOLE SIZE REQUIRED | A INSIDE DIAMETER | B HEAD DIAMETER |
|----------|--------------------|-------------------|-----------------|
| 8490     | .375 (9.5)         | .265 (6.7)        | .421 (10.7)     |
| 8491     | .500 (12.7)        | .312 (7.9)        | .562 (14.3)     |
| 8492     | .562 (14.3)        | .390 (9.9)        | .640 (16.3)     |
| 8493     | .625 (15.9)        | .453 (11.5)       | .687 (17.4)     |
| 8494     | .750 (19.1)        | .546 (13.9)       | .796 (20.2)     |
| 8495     | .875 (22.2)        | .671 (17.0)       | .921 (23.4)     |
| 8496     | 1.000 (25.4)       | .796 (20.2)       | 1.062 (27.0)    |

## NYLON INSULATING BUSHINGS

Snaps into panel hole to provide protection for wire, cable and tubing from sharp uneven edges.



**MATERIAL:** Nylon 6/6, Black

| CAT. NO. | HOLE SIZE REQUIRED | MAXIMUM CHASSIS THICKNESS | A INSIDE DIAMETER | B HEAD DIAMETER | C OVERALL HEIGHT |
|----------|--------------------|---------------------------|-------------------|-----------------|------------------|
| 8470     | .250 (6.4)         | .062 (1.57)               | .125 (3.2)        | .312 (7.9)      | .312 (7.9)       |
| 8471     | .312 (7.9)         | .062 (1.57)               | .187 (4.7)        | .375 (9.5)      | .312 (7.9)       |
| 8472     | .375 (9.5)         | .125 (3.2)                | .250 (6.4)        | .468 (11.9)     | .406 (10.3)      |
| 8473     | .437 (11.1)        | .125 (3.2)                | .312 (7.9)        | .531 (13.5)     | .406 (10.3)      |
| 8474     | .500 (12.7)        | .125 (3.2)                | .375 (9.5)        | .578 (14.7)     | .406 (10.3)      |
| 8475     | .562 (14.3)        | .125 (3.2)                | .437 (11.1)       | .656 (16.7)     | .406 (10.3)      |
| 8476     | .625 (15.9)        | .125 (3.2)                | .500 (12.7)       | .718 (18.2)     | .406 (10.3)      |
| 8477     | .750 (19.1)        | .125 (3.2)                | .562 (14.3)       | .843 (21.4)     | .406 (10.3)      |
| 8478     | .875 (22.2)        | .125 (3.2)                | .625 (15.9)       | .953 (24.2)     | .453 (11.5)      |
| 8479     | 1.000 (25.4)       | .125 (3.2)                | .750 (19.1)       | 1.125 (28.6)    | .453 (11.5)      |
| 8480     | 1.187 (30.1)       | .125 (3.2)                | .937 (23.8)       | 1.312 (33.3)    | .453 (11.5)      |
| 8481     | 1.250 (31.8)       | .125 (3.2)                | .937 (23.8)       | 1.359 (34.5)    | .453 (11.5)      |
| 8482     | 1.375 (34.9)       | .125 (3.2)                | 1.000 (25.4)      | 1.468 (37.3)    | .453 (11.5)      |
| 8483     | 1.500 (38.1)       | .125 (3.2)                | 1.062 (27.0)      | 1.609 (40.9)    | .453 (11.5)      |
| 8484     | 1.750 (44.5)       | .125 (3.2)                | 1.375 (34.9)      | 1.875 (47.6)    | .453 (11.5)      |
| 8485     | 2.000 (50.8)       | .125 (3.2)                | 1.625 (41.3)      | 2.125 (54.0)    | .453 (11.5)      |
| 8486     | 2.500 (63.5)       | .250 (6.4)                | 1.968 (50.0)      | 2.656 (67.5)    | .718 (18.2)      |