




|             |           |           |            |
|-------------|-----------|-----------|------------|
| Farnell NO. | 8706646   | 8706654   | 8706662    |
| L ± T (mm)  | 500 ± 5   | 1000 ± 10 | 2000 ± 20  |
| Farnell NO. | 8706670   | 8706689   | 8706697    |
| L ± T (mm)  | 3000 ± 30 | 5000 ± 40 | 10000 ± 70 |



NOTE:

- (1). Cable Wiring: CAT. 5E UTP Stranded 24AWG(7\*0.18CU)\*4P  
Jacket Material:LSOH OD:5.0 ± 0.20mm  
Cable Colour:GREY  
Cable Printing: System Cable UTP CAT 5E 4 Pairs 24AWG  
Stranded ISO 11801 100MHz
- (2). Connector A&B: RJ45(8P8C) Male Type  
INSULATION:Clear Polyester  
CONTACTS:Brass,Gold Plated
- (3). Over Mold: PVC, GREY
- (4). Parameter Settings: UT8080M  
1. Conductive Resistance:1kΩ  
2. Insulative Resistance:5MΩ (Min.)
- (5). Packing: POLYBAG PACKING



PIN OUT: (4)

PACKING: (5)

GENERAL TOLERANCES  
(UNLESS SPECIFIED)

Pro-SIGNAL

LENGTH: X. ± 1

UNIT: mm

REV: 0/A



NAME

CAT. 5E UTP CABLE(24AWG CU)

ANGLE: X° . ± 1°

DRAWING

2012/01/10

S. P. NO.

DWG. NO.

REV

DATE

APPROVE

SIZE

PAGE

1/1