





REVISIONS				
ISS	ZONE	DESCRIPTION\PER	REQUEST\	DATE



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. BERYLLIUM COPPER PER QQ-C-530
3. TEFLON PER MIL-P-19468
4. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
5. SILVER PL. 200 MIN. THICK OVER COPPER STRIKE

DIMENSIONS ARE IN MILLIMETERS					PART NO.		Amphenol Danbury,CT,USA-Tainan,Taiwan-Shenzhen,China	
UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4					APPROVED	DATE		
					CHECKED	DATE		
					DRAWN	DATE		
SCALE 3/1 ISSUE A1					FILE NO. F:\DWG\CNPD\27075SZ		TITLE MHV CABLE JACK FOR RG-59/U-62/U CABLE	
6	CLAMP NUT	NOTE 1	NOTE 4	1	31-1428-3	DRAWING NO. 27075		ITEM NO. 27075
5	GASKET	SILICONE	RED	1	31-1051-2			
4	BRAID CLAMP	NOTE 1	NOTE 4	1	82-1551-3			
3	CONTACT PIN	NOTE 2	NOTE 5	1	28178			
2	INSULATOR	NOTE 3	NATURAL	1	28179			
1	BODY	NOTE 1	NOTE 4	1	31-11303			