





REV.	DATE	DESCRIPTION
C	02/18/03	UPDATE DRAWING FORMAT
D	07/31/05	ADD "DOUBLE BRAID CABLE" TO DESCRIPTION



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .151"
 2. CONTACT PIN TO SOLDER

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex								
8	HEAT SHRINK TUBE		BLACK	1		DRAWN	G.R.S.	07/31/05										
7	FERRULE	COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED				PART DESCRIPTION SMA R/A CRIMP PLUG (FOR RG-316/U DOUBLE BRAID CABLE)								
6	COVER	BRASS	GOLD	1		ISSUED												
5	GASKET	SILICONE	RED	1		SHEET		1 OF 1										
4	RETAINER RING	BER. COPPER	NATURAL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”					PART NO. 132182								
3	CONTACT PIN	BRASS	GOLD	1														
2	INSULATOR	TEFLON	NATURAL	1														
1	HOUSING/BODY	BRASS	GOLD	1		CAD FILE		C:/132/132182.DWG		DWG. NO.		132182.DWG	REV.	D	SIZE	A	SCALE	NA
DESCRIPTION				MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING											