

[Twisted Pair & Flat
Phone Cable](#)[Fiber Optic Cable](#)[Coaxial Cable](#)[Electrical and Industrial](#)[Bench/Other Hand Tools](#)[What's New](#)[Coaxial Cable > Crimpers > 1300 Series](#)[We also suggest](#)

BNC/TNC & Mini-UHF 1300 Series Crimper

Part number: 1336  Technical

Part numbers

Tool & Die: 1336

Die only: 2047

Description

Crimps BNC/TNC & mini-UHF 50 & 75 ohm coaxial connectors.

Type

RG59, RG62, Belden 8281 & 1505A

Crimp size

.315/.252/.068" HEX & .042" SQ

Connector style

Kings, ADC, Amphenol, etc.



PowerPlay® PT-
540



Double 110
Blade-
SurePunch® &
SurePunch® Pro



GripP Wire
Stripper Bundle
(30-10 AWG)



SealTite® Pro
Compression
Crimper - RCA,
BNC, Cable TV F
(RG59/6/6 Quad)



Combo
UTP/Coax
SureStrip®
Cutter/Stripper