

MICRO SWITCHA DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING

JS-68

5

JS-68**M**DRAWING
NUMBER

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

REPLACES

RELEASE NO. SR7058

CHECK

OCT. 59

OCT. 59

JAN 72

DEC 92

MAR 95

OCT. 59

OCT. 59

OCT. 59

OCT. 59

OCT. 59

OCT. 59

OCT. 59

OCT. 59

OCT. 59

480 APPROX
FREE POSITIONA
.340±.030
OPERATING POSITION

.22

.09

FLEXIBLE INSULATOR

REF

.375

.20

REF

.781

NOTE-



FURNISHED UNASSEMBLED

2-56 NC HEX NUT (2) 1

2-56 NC X .500 REF ROUND HEAD
MACHINE SCREW (2) 1

SPRING LOCKWASHER (2) 1

.16

.14

.266

REF

CORROSION RESISTANT
STEEL ACTUATOR.DOTTED LINES INDICATE
BASIC SWITCH IN PLACE.

.012

REF

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF
HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.**CHARACTERISTICS** WITH ISM BASIC
SWITCH INSTALLED

OPERATING FORCE - - - - - 9 OZ. MAX.

RELEASE FORCE - - - - - 2 OZ. MIN.

PRETRAVEL - - - - - .218 MAX.

DIFFERENTIAL TRAVEL - - - .020 MAX.

OVERTRAVEL - - - - - .030 MIN.

ELECTRICAL DATA

CONTACT ARRANGEMENT

BREAK DISTANCE

SCALE-FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES**TOLERANCES ARE:**ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT

A

FO-50378

DRAWN

K. A. F.

30 OCT. 57

CHECK