























Amp	Volt	Hz	IP Ident. colour + h	Part No.	Wall socket outlets 3 P + N +  IEC/EN 60 309	  9	EAN-No. 4015609...																														
 IP44					external fixing means, 1 top cable entry	10/60 227	000012 009091 009138 009152																														
16	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	110 110 504 110 509 110 511	   <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>60</td><td>5,3</td><td>80</td><td>74</td><td>90</td><td>31</td><td>129</td><td>16</td></tr><tr><td>32 A</td><td>60</td><td>5,3</td><td>97</td><td>82</td><td>105</td><td>45</td><td>155</td><td>21</td></tr></table>			Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	90	31	129	16	32 A	60	5,3	97	82	105	45	155	21			
Ampère	b	c	d	e	f	l	n	Pg																													
16 A	60	5,3	80	74	90	31	129	16																													
32 A	60	5,3	97	82	105	45	155	21																													
32	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	130 130 504 130 509 130 511	   <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>60</td><td>5,3</td><td>80</td><td>74</td><td>90</td><td>31</td><td>129</td><td>16</td></tr><tr><td>32 A</td><td>60</td><td>5,3</td><td>97</td><td>82</td><td>105</td><td>45</td><td>155</td><td>21</td></tr></table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	90	31	129	16	32 A	60	5,3	97	82	105	45	155	21	10/60 320	000081 010585 010622 010646			
Ampère	b	c	d	e	f	l	n	Pg																													
16 A	60	5,3	80	74	90	31	129	16																													
32 A	60	5,3	97	82	105	45	155	21																													
 IP44					red special version, external fixing means, 1 top cable entry	10/60 227	000036																														
16	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	113 113 504 113 509 113 511	   <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>60</td><td>5,3</td><td>80</td><td>74</td><td>90</td><td>31</td><td>129</td><td>16</td></tr><tr><td>32 A</td><td>60</td><td>5,3</td><td>97</td><td>82</td><td>105</td><td>45</td><td>155</td><td>21</td></tr></table>			Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	90	31	129	16	32 A	60	5,3	97	82	105	45	155	21			
Ampère	b	c	d	e	f	l	n	Pg																													
16 A	60	5,3	80	74	90	31	129	16																													
32 A	60	5,3	97	82	105	45	155	21																													
32	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	133 133 504 133 509 133 511	   <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>60</td><td>5,3</td><td>80</td><td>74</td><td>90</td><td>31</td><td>129</td><td>16</td></tr><tr><td>32 A</td><td>60</td><td>5,3</td><td>97</td><td>82</td><td>105</td><td>45</td><td>155</td><td>21</td></tr></table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	90	31	129	16	32 A	60	5,3	97	82	105	45	155	21	10/60 320	000104			
Ampère	b	c	d	e	f	l	n	Pg																													
16 A	60	5,3	80	74	90	31	129	16																													
32 A	60	5,3	97	82	105	45	155	21																													
 IP44					internal fixing means, 2 cable entries both, top and bottom (knock-out)	5 425	000029 009411 009435 009459																														
16	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	111 111 504 111 509 111 511	   <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>146</td><td>47,5</td><td>164</td><td>7</td><td>16/21</td></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>157</td><td>47,5</td><td>173</td><td>7</td><td>16/21</td></tr></table>			Ampère	b	c	d	e	f	l	n	v	Pg	16 A	66,5	5	96	95	146	47,5	164	7	16/21	32 A	66,5	5	96	95	157	47,5	173	7	16/21
Ampère	b	c	d	e	f	l	n	v	Pg																												
16 A	66,5	5	96	95	146	47,5	164	7	16/21																												
32 A	66,5	5	96	95	157	47,5	173	7	16/21																												
32	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	131 131 504 131 509 131 511	   <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>146</td><td>47,5</td><td>164</td><td>7</td><td>16/21</td></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>157</td><td>47,5</td><td>173</td><td>7</td><td>16/21</td></tr></table>	Ampère	b	c	d	e	f	l	n	v	Pg	16 A	66,5	5	96	95	146	47,5	164	7	16/21	32 A	66,5	5	96	95	157	47,5	173	7	16/21	5 489	000098 010837 010844 010851
Ampère	b	c	d	e	f	l	n	v	Pg																												
16 A	66,5	5	96	95	146	47,5	164	7	16/21																												
32 A	66,5	5	96	95	157	47,5	173	7	16/21																												
 IP67					internal fixing means, cable entries: 1 x top (open), 2 x bottom (knock-out) and vice versa	2 1105	000159 011407 011438 011452																														
63	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	161 161 504 161 509 161 511	   <table><tr><th>Part</th><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>n</th><th>v</th><th>Pg</th></tr><tr><td>161</td><td>63 A</td><td>136</td><td>104</td><td>4,2</td><td>172</td><td>121</td><td>178</td><td>220</td><td>5</td><td>29</td></tr></table>			Part	Ampère	a	b	c	d	e	f	n	v	Pg	161	63 A	136	104	4,2	172	121	178	220	5	29								
Part	Ampère	a	b	c	d	e	f	n	v	Pg																											
161	63 A	136	104	4,2	172	121	178	220	5	29																											
 IP67					internal fixing means, cable entries: 1 x top (open), 2 x bottom (knock-out) and vice versa	2 1900	000159 011407 011438 011452																														
125	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	163 163 504 163 509 163 511	   <table><tr><th>Part</th><th>Amp.</th><th>a</th><th>b</th><th>b1</th><th>c</th><th>d</th><th>e</th><th>f</th><th>n</th><th>Pg</th></tr><tr><td>163</td><td>63 A</td><td>183</td><td>151</td><td>114</td><td>6,5</td><td>237</td><td>183</td><td>196</td><td>302</td><td>21/29</td></tr></table>			Part	Amp.	a	b	b1	c	d	e	f	n	Pg	163	63 A	183	151	114	6,5	237	183	196	302	21/29								
Part	Amp.	a	b	b1	c	d	e	f	n	Pg																											
163	63 A	183	151	114	6,5	237	183	196	302	21/29																											

see page 2/20