

T40R0M4

Cable Tie. 40 lb. 8.27" Max. Bun. Dia. 2.16" PA66, Black, 1000/pk

Article Number: 111-04122

Part Number: T40R0M4

Type: T40R(U)


Material: PA66



1. Base Data

|                    |                                                                                                                                                                                                                           |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part No.           | T40R0M4                                                                                                                                                                                                                   |
| Type               | T40R(U)                                                                                                                                                                                                                   |
| Color              | Black (BK)                                                                                                                                                                                                                |
| Features           | HellermannTyton manufactures a full line of high quality cable ties in a variety of styles, sizes, materials, and colors. HellermannTyton cable ties are engineered and manufactured for maximum performance and quality. |
| Application        | Used to bundle and secure wire and cable.                                                                                                                                                                                 |
| Application Method | Quick, simple application by hand or with HellermannTyton tensioning tools.                                                                                                                                               |

## 2. Product Dimensions



|                       |                  |
|-----------------------|------------------|
| Min. Tensile Strength | 40 lbs / 180 N   |
| Length (L)            | 8.27 " / 210 mm  |
| Width (W)             | .16 " / 4.0 mm   |
| Min. Ø Bundle         | .06 " / 1.5 mm   |
| Max. Ø Bundle         | 2.16 " / 55.0 mm |

## 4. Material and Specifications

|                       |                                                                                     |
|-----------------------|-------------------------------------------------------------------------------------|
| Material              | Polyamide 6.6 (PA66)                                                                |
| Material Shortcut     | PA66                                                                                |
| Flammability          | UL94 V2                                                                             |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C)<br>continuous                                  |
| ROHS Conformity       |  |

## Logistic and Packaging

|                |               |
|----------------|---------------|
| Packaging Type | bag           |
| Pkg. Qty.      | 1000          |
| Carton Qty.    | 5000          |
| EAN code       | 4031026274645 |

UPC

08930608017

Miscellaneous


UL Listed (US and Canada) Yes

UL Recognized (US and Canada) Yes

## Standard Cable Ties

### T40 - T50 Series - Natural and Black

| Material Data         |                                                 |
|-----------------------|-------------------------------------------------|
| Material              | Polyamide 6.6 (PA66)                            |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C) continuous |
| Flammability          | UL94 V2                                         |



File# E64139



File# E64139

| Product Selection |          |         |                     | File# E64139          |       |            |       |               |       |           |       | File# E64139 |           |
|-------------------|----------|---------|---------------------|-----------------------|-------|------------|-------|---------------|-------|-----------|-------|--------------|-----------|
| Article No.       | Part No. | Type    | US Gov. Designation | Min. Tensile Strength |       | Length (L) |       | Max. Ø Bundle |       | Width (W) |       | Color        | Pkg. Qty. |
|                   |          |         |                     | lbs.                  | (N)   | in.        | (mm)  | in.           | (mm)  | in.       | (mm)  |              |           |
| T40R              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 112-04019         | T40R9C2  | T40R(U) | —                   | 40 lbs                | (180) | 8.27"      | (210) | 2.16"         | (55)  | .16"      | (4.0) | Natural      | 100       |
| 111-04131         | T40R9M4  | T40R(U) | —                   | 40 lbs                | (180) | 8.27"      | (210) | 2.16"         | (55)  | .16"      | (4.0) |              | 1000      |
| 112-04060         | T40R0C2  | T40R(U) | —                   | 40 lbs                | (180) | 8.27"      | (210) | 2.16"         | (55)  | .16"      | (4.0) | Black        | 100       |
| 111-04122         | T40R0M4  | T40R(U) | —                   | 40 lbs                | (180) | 8.27"      | (210) | 2.16"         | (55)  | .16"      | (4.0) |              | 1000      |
| T40I              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 111-04609         | T40I9C2  | T40I    | —                   | 40 lbs                | (180) | 11.42"     | (290) | 3.15"         | (80)  | .16"      | (4.0) | Natural      | 100       |
| 111-04612         | T40I9M4  | T40I    | —                   | 40 lbs                | (180) | 11.42"     | (290) | 3.15"         | (80)  | .16"      | (4.0) |              | 1000      |
| 111-04600         | T40I0C2  | T40I    | —                   | 40 lbs                | (180) | 11.42"     | (290) | 3.15"         | (80)  | .16"      | (4.0) | Black        | 100       |
| 111-04604         | T40I0M4  | T40I    | —                   | 40 lbs                | (180) | 11.42"     | (290) | 3.15"         | (80)  | .16"      | (4.0) |              | 1000      |
| T40L              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 111-04300         | T40L9C2  | T40L    | —                   | 40 lbs                | (180) | 14.4"      | (365) | 4.13"         | (105) | .16"      | (4.0) | Natural      | 100       |
| 111-04311         | T40L9M4  | T40L    | —                   | 40 lbs                | (180) | 14.4"      | (365) | 4.13"         | (105) | .16"      | (4.0) |              | 1000      |
| 111-04301         | T40L0C2  | T40L    | —                   | 40 lbs                | (180) | 14.4"      | (365) | 4.13"         | (105) | .16"      | (4.0) | Black        | 100       |
| 111-04305         | T40L0M4  | T40L    | —                   | 40 lbs                | (180) | 14.4"      | (365) | 4.13"         | (105) | .16"      | (4.0) |              | 1000      |
| T50S              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 111-05811         | T50S9C2  | T50S    | —                   | 50 lbs                | (225) | 5.9"       | (150) | 1.38"         | (35)  | .18"      | (4.6) | Natural      | 100       |
| 111-05813         | T50S9M4  | T50S    | —                   | 50 lbs                | (225) | 5.9"       | (150) | 1.38"         | (35)  | .18"      | (4.6) |              | 1000      |
| 111-05806         | T50S0C2  | T50S    | —                   | 50 lbs                | (225) | 5.9"       | (150) | 1.38"         | (35)  | .18"      | (4.6) | Black        | 100       |
| 111-05808         | T50S0M4  | T50S    | —                   | 50 lbs                | (225) | 5.9"       | (150) | 1.38"         | (35)  | .18"      | (4.6) |              | 1000      |
| T50R              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 112-05019         | T50R9C2  | T50R    | MS3367-1-9          | 50 lbs                | (225) | 7.9"       | (200) | 1.97"         | (50)  | .18"      | (4.6) | Natural      | 100       |
| 111-04862         | T50R9M4  | T50R    | MS3367-1-9          | 50 lbs                | (225) | 7.9"       | (200) | 1.97"         | (50)  | .18"      | (4.6) |              | 1000      |
| 111-04878         | T50R0C2  | T50R    | *                   | 50 lbs                | (225) | 7.9"       | (200) | 1.97"         | (50)  | .18"      | (4.6) | Black        | 100       |
| 111-04846         | T50R0M4  | T50R    | *                   | 50 lbs                | (225) | 7.9"       | (200) | 1.97"         | (50)  | .18"      | (4.6) |              | 1000      |
| T50I              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 112-05219         | T50I9C2  | T50I    | MS3367-7-9          | 50 lbs                | (225) | 11.8"      | (300) | 3.35"         | (85)  | .18"      | (4.6) | Natural      | 100       |
| 111-05230         | T50I9M4  | T50I    | MS3367-7-9          | 50 lbs                | (225) | 11.8"      | (300) | 3.35"         | (85)  | .18"      | (4.6) |              | 1000      |
| 111-00444         | T50I0C2  | T50I    | *                   | 50 lbs                | (225) | 11.8"      | (300) | 3.35"         | (85)  | .18"      | (4.6) | Black        | 100       |
| 111-05216         | T50I0M4  | T50I    | *                   | 50 lbs                | (225) | 11.8"      | (300) | 3.35"         | (85)  | .18"      | (4.6) |              | 1000      |
| T50L              |          |         |                     |                       |       |            |       |               |       |           |       |              |           |
| 112-05419         | T50L9C2  | T50L    | MS3367-2-9          | 50 lbs                | (225) | 15.35"     | (390) | 4.33"         | (110) | .18"      | (4.6) | Natural      | 100       |
| 111-05449         | T50L9M4  | T50L    | MS3367-2-9          | 50 lbs                | (225) | 15.35"     | (390) | 4.33"         | (110) | .18"      | (4.6) |              | 1000      |
| 111-00445         | T50L0C2  | T50L    | *                   | 50 lbs                | (225) | 15.35"     | (390) | 4.33"         | (110) | .18"      | (4.6) | Black        | 100       |
| 111-00504         | T50L0M4  | T50L    | *                   | 50 lbs                | (225) | 15.35"     | (390) | 4.33"         | (110) | .18"      | (4.6) |              | 1000      |

Installation tools - MK7, MK7HT, MK7P, MK9, MK9HT, MK9P. Dimensions are approximate and subject to technical changes.

Use **Part No.** for ordering and **Type** for specification purposes.

\* Military black available. Contact HellermannTyton for more information.