



LOCKING CIRCUIT BOARD SUPPORTS

CBSP
PCB Spring Spacer

As Molded



Assembled

Top Hole:
Snap-lock: .189 (4.8)
Panel Thickness:
.062 (1.57)



Bottom Hole:
Snap-lock: .189 (4.8)
Panel Thickness:
.062 (1.57)

New

Richco®

- When pin is inserted into spacer, part flexes and acts as a plastic spring
- One piece design reduces the need for hardware
- Provides continuous support to PCB
- Keeps light sensors on the PCB in constant contact with touch control cover
- Material: UL94 HB Acetal
- Color: Natural

Item No.	Bulk Pack Qty.
CBSP-1	1000

CBSPM
Rubber Pull Mount Circuit Board Support

Top Hole:
Snap-fit: .187 (4.75)
Panel Thickness:
.094 (2.4) Max

Bottom Hole:
Snap-fit: .187 (4.75)
Panel Thickness:
.094 (2.4) Max

New

Richco®


- Rubber spacer provides shock and vibration protection
- Pull mount ends are easily fed into panel holes and pulled into a locked position
- Once installed, the ends are easily cut off leaving low profile mounting ends
- Material: EPDM, 45 Shore A
- Color: Black

Item No.	"A" Standoff Height	Bulk Pack Qty.
CBSPM-4	.250 (6.35)	500
CBSPM-6	.375 (9.53)	500
CBSPM-8	.500 (12.7)	500
CBSPM-10	.625 (15.88)	500
CBSPM-12	.750 (19.05)	500

LCBS Series
Locking Support

Specifications:

- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94 V-2




To Lock in Hole:
Snap-fit: .156 (4)
Panel Thickness:
.047-.067 (1.2-1.7)

To Lock in Hole:
Snap-fit: .187 (4.8)
Panel Thickness:
.031-.078 (0.8-2.0)

Item No.	In	A mm	Bulk Pack Qty.
CBLS005A	0.138	3.5	1000
LCBS-3-01	0.187	4.8	1000
LCBS-6M-01	0.236	6.0	1000
LCBS-4-01	0.250	6.4	1000
LCBS-5-01	0.312	7.9	1000
LCBS-6-01	0.375	9.5	1000
LCBS-7-01	0.437	11.1	1000
LCBS-8-01	0.500	12.7	1000
LCBS-10-01	0.625	15.9	1000

Item No.	In	A mm	Bulk Pack Qty.
LCBS-12-01	0.750	19.1	1000
LCBS-14-01	0.875	22.2	1000
CBLS060A	0.945	24.0	1000
LCBS-16-01	1.000	25.4	1000
LCBS-18-01	1.125	28.6	1000
CBLS075A	1.224	31.1	1000
LCBS-20-01	1.250	31.7	1000
LCBS-22-01	1.375	34.9	1000




Top Hole:
Snap-lock: .156 (4.0)
Panel Thickness: .062 (1.57)

Bottom Hole:
Snap-lock: .187 (4.8)
Panel Thickness: .031 - .078 (.79 - 1.98)

Item No.	UL94 V-0	A In	A mm	Bulk Pack Qty.
LCBS2-3-01	LCBS2-3-19	0.188	4.8	1000
LCBS2-4-01	LCBS2-4-19	0.250	6.4	1000
LCBS2-5-01	LCBS2-5-19	0.313	7.9	1000
LCBS2-6-01	LCBS2-6-19	0.375	9.5	1000
LCBS2-7-01	LCBS2-7-19	0.438	11.1	1000
LCBS2-8-01	LCBS2-8-19	0.500	12.7	1000
LCBS2-10-01	LCBS2-10-19	0.625	15.9	1000

Item No.	UL94 V-2	A In	A mm	Bulk Pack Qty.
LCBS2-12-01	LCBS2-12-19	0.750	19.1	1000
LCBS2-14-01	LCBS2-14-19	0.875	22.2	1000
LCBS2-16-01	LCBS2-16-19	1.000	25.4	1000
LCBS2-18-01	LCBS2-18-19	1.125	28.6	1000
LCBS2-20-01	LCBS2-20-19	1.250	31.8	1000
LCBS2-22-01	LCBS2-22-19	1.375	34.9	1000



Top Hole:
Snap-fit: .156 (4.0)
Panel Thickness: .062 (1.57)

Bottom Hole:
Snap-lock: .187 (4.8)
Panel Thickness: .031 - .078 (0.8 - 2.0)

Item No.	A In	A mm	Bulk Pack Qty.
LNCBS-3-01	0.188	4.8	1000
LNCBS-4-01	0.250	6.4	1000
LNCBS-6-01	0.375	9.5	1000
LNCBS-8-01	0.500	12.7	1000

Item No.	A In	A mm	Bulk Pack Qty.
LNCBS-10-01	0.625	15.9	1000
LNCBS-12-01	0.750	19.1	1000
LNCBS-14-01	0.875	22.2	1000

Richco®

Richco®