



Magna Deluxe 20" Lamp

A whole new class of elegant looking fluorescent light from Aven designed to give you crisp, flicker-free lighting, and a maximum uniformity together with a larger lighting area. The 20" lighting head is totally enclosed and features a 55 watt fluorescent bulb. Features a built-in electronic ballast for increased lumen.

The heavy duty industrial grade adjustable arm with tempered steel springs and tension control knobs allows you to easily position the lamp where you want it. The head swivels 310° and tilts 210° for maximum adjustment. Comes with a mounting clamp and a 5ft power cord. Operates 115 VAC. 1 year warranty (excludes bulb).

MAGNA DELUXE 20" FLUORESCENT LAMP

LIGHTING HEAD	20in
POWER CORD	5ft
OPERATING VOLTAGE	115 VAC
WARRANTY	1 Year (excludes bulb)

Part #	Description
26516-D155	Magna Deluxe 20" Fluorescent Lamp

Task Lamps Fluorescent



Magna Deluxe XL 3 Tube Lamp

Features:

- 45W fluorescent lamp (3 tubes, 15 Watts each) for demanding visual tasks
- Switches allow you to turn on one, two, or three lamps to suit your needs
- Spring balanced 35" arm allows rapid positioning of the light and will stay in position needed for your application
- All metal construction with baked on enamel finish
- Built-in electronic ballast
- C-clamp included for mounting to tables up to 2" thick
- 3-cord plug

Part #	Description
26516-D3T	Magna Deluxe XL 3 Tube Fluorescent Lamp



Sirius Flex Arm Task Light

Excellent for all types of applications requiring high intensity illumination, such as manufacturing, assembly, and inspection. Flex arm for infinite adjustments. Lamp Head can be moved in up and down direction. 20 Watt Halogen bulb included. Arm size of 520mm (20.5") Can accept up to 50 watt bulb. C-Clamp is included. Optional Magnetic Base also available. Industrial Grade Quality.

Part #	Description
26525	Sirius Flex Arm Task Light
26520-MB	Sirius Magnetic Base