

FPC-7700

Robust Box PC with Intel® Sandy Bridge / Ivy Bridge Platform



Features

- **Fanless Design**
- Wide Range DC Power Input (9 ~36V)
- Support iAMT Function
- Support Various Video Interfaces (DVI-I + DVI-D)
- Support Optional WiFi or HSUPA Wireless Connectivity
- Rugged Design for Shock/Vibration Protection
- Memory Support up to 16GB (DDR3)
- Intel® SSD compatible

System

CPU	Support Intel® 2nd & 3rd generation Core™ i7/i5/i3 or Celeron® processors in rPGA988 socket
Memory	2 x 204-pin DDR3 SO-DIMM sockets, supporting 1333/1600MHz SDRAM up to 16GB
Chipset	Intel® QM77
Graphics	Integrated Intel® HD 4000
ATA	2 x Serial ATA ports with RAID 0/1 support 2 x eSATA
LAN Chipset	2 x Intel® WG82583V GbE controllers 1 x Intel® WG82579LM GbE PHY w/ iAMT
Watchdog Timer	1~255 levels reset

I/O

Serial Port	1 x DB-44 female connector COM1/2 are RS-232 COM3/4 are RS-232/422/485 selectable, w/ 2.5kv isolation protection
USB Port	6 x USB 2.0 ports, 4 x USB 3.0/ 2.0 ports
LAN	3 x RJ-45 ports for GbE
Video Port	1 x DVI-I female connector for Digital/ Analog Video output 1 x DVI-D female connector for Digital Video output
Selectable Port	1 x DB25 connector for 1 x DIO (8 in/8 out) port or 1 x LPT port (either one) DIO by default, can be changed to LPT
Audio	Mic-in/Line-out
Expansion Bus	1 x Mini-card slot interconnected with SIM card socket for optional WiFi or HSUPA module 1 x SIM socket/1 x CFast socket (outside accessible)

Environmental

Operating Temp.	-20 ~ 55°C (-4 ~ 131°F), ambient w/ air flow
Storage Temp.	-40 ~ 85°C (-40 ~ 185°F)
Operating Humidity	10 ~ 95% @ 55°C (non-condensing)
Vibration	3 Grms/5~500Hz/random operation w/ SSD

Shock

Operating 40G (11ms), Non-operating 60G with SSD
Crash 100G, 11ms

Qualification

Certification CE, FCC Class A

Power Requirement

Power Input DC 9~36V input w/ 4-pin terminal block
Power Consumption 3.51A/19V, 67W (i7-3610QE)

Storage

Type 2 x 2.5" drive bays
1 x CFast socket

Mechanical

Construction Aluminum alloy
Mounting Support wall-mounting
Weight 6.4 kg (14.1 lb)
Dimensions (W x D x H) 225 x 267 x 90 mm

OS Support

Windows XP Professional / Windows Embedded Professional 7 / Windows Embedded Standard 7


Ordering Information

FPC-7700 Fanless system w/o expansion



» Fanless Design

Dimensions



Optional Accessories

PAC-B120W-FSP

19V/6.32A 120W AC/DC adapter kit



CBL-7100-COM

4 x COM ports converter cable



WMK-7000


Wall-mount kit for FPC-7XXX Series



Optional Configuration (CTOS* Kit)


SSD-25040

Intel® 2.5" 40GB SATAII SSD kit



HSPA-SI1400

HSUPA 3.75G module kit & internal wiring



WIFI-IN1300

Intel® Centrino® Advanced-N 6205 WiFi module w/ 20cm internal wiring



ANT-H11

1 x 2dBi HSUPA antenna



ANT-D11

1 x WiFi Dual-band 2.4G/5G antenna



Core™ i3-3120ME

Intel® 3rd Gen. Core™ i3-3120ME processor, L2/3M, 2.4G

Core™ i5-3610ME

Intel® 3rd Gen. Core™ i5-3610ME processor, L2/3M, 2.7G

Core™ i7-3610QE

Intel® 3rd Gen. Core™ i7-3610QE processor, L2/6M, 2.3G



MK-3C-4G-1

DDR3-1333 4GB SDRAM DIMM1 kit

MK-3C-4G-2

DDR3-1333 4GB SDRAM DIMM2 kit

MK-3C-8G-1

DDR3-1600 8GB SDRAM DIMM1 kit

MK-3C-8G-2

DDR3-1600 8GB SDRAM DIMM2 kit



*CTOS means Configure to Order Service.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ARBOR Technology:](#)

[FPC-7700](#)