




PRINT: 5:1





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E10		LASER PRINT UPDATED	04DEC2017	Sz	LSz
E11		DIVERGENT MARKING ADDED	18JUL2018	LSz	SzN
E12		LASER PRINT UPDATED WITH BR VERSION	19NOV2018	SZN	LSZ
E13		DIVERGENT MARKING ADDED	13FEB2025	SZN	LSZ

CODINGS
M 2:1



- 1 AREA FOR PRINT
- 2 USABLE CONTACTS MCON 1.2 LL
SEE TE-NO. 1452674, SINGLE WIRE SYSTEM
- 3 MAX. WIRE SIZE RANGE 1.5 mm² FLR PERMITTED WITH COMPATIBLE SWS
FOR CAVITY-Ø 3.55MM
FOR PERMISSIBLE CURRENT CARRYING CAPACITY OF THE SINGLE CONTACT,
MAX OPERATING TEMPERATURE, VIBRATION RESISTANCE
SEE PRODUCT SPECIFICATION NO.108-18782
- 4 SUPPLIER-MARK
- 5 SPACE OF ACTIVITY
- 6 SUPPLY CONDITION: CPA IN PRELOCKED POSITION
- 7 SUPPLY CONDITION: RETAINER IN PRELOCKED POSITION
- 8 WARPAGE PERMITTED TO MAX. -0.5mm
- 9 TE ORDER-NO.
- 10 ACCORDING TO INTERFACE DRAWING
SEE TE-NO. 114-18679-3
- 11 ASSEMBLY LINE SEGMENT IDENTIFICATION
- 12 DATE CODE (DDDDYY)
- 13 DIVERGENT MARKING FOR PARTS PRODUCED IN DIFFERENT REGIONS



RETAINER IN END POSITION

CPA IN END POSITION

A-A
3:1



B-B
3:1

3D VIEW
1:1

1:1


THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C. L'Abbate 18OCT2004		 TE Connectivity	
DIMENSIONS: mm			CHK A. Schroebl 13JAN2005			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 1-PLC 2-PLC 3-PLC 4-PLC ANGLES FINISH 100% 100% 100% 100% 100% 100% 100% 100% 100%					

E11 Divergent marking is allowed for parts from different tools



- | | |
|---|--|
|  | TE PART NO.: |
|  | - CIRCULAR DATE INSERT ONLY FOR VERSION 1
- DATE FORMAT FOR VERSION 2 (YY/MM) |
|  | REVISION, CORRESPONDING TO ACTUAL REVISION |
|  | MATERIAL IDENTIFICATION |
|  | MOULD CAVITY IDENTIFICATION |
|  | DATE INSERT FOR RECEPTACLE HOUSING |

3-1718643-4	C	CONNECTOR 2POS.	A	1	CPA	PA46-GF15	RED SIML. RAL 3000	5	
				1	SEAL	MVQ	NATURE -	4	
				1	RETAINER	PA66-GF15	VIOLETT SIML. RAL 4006	3	
				1	OUTER HOUSING	PA6-GF15	SULFUR YELLOW SIML. RAL 1016	2	
				1	INNER HOUSING	PA66-GF30	BLUE SIML. RAL 5012	1	
2-1718643-4	B	CONNECTOR 2POS.	A	1	CPA	PA46-GF15	RED SIML. RAL 3000	5	
				1	SEAL	MVQ	NATURE -	4	
				1	RETAINER	PA66-GF15	VIOLETT SIML. RAL 4006	3	
				1	OUTER HOUSING	PA6-GF15	SULFUR YELLOW SIML. RAL 1016	2	
				1	INNER HOUSING	PA66-GF30	NATURE	1	
1-1718643-4	A	CONNECTOR 2POS.	A	1	CPA	PA46-GF15	RED SIML. RAL 3000	5	
				1	SEAL	MVQ	NATURE -	4	
				1	RETAINER	PA66-GF15	VIOLETT SIML. RAL 4006	3	
				1	OUTER HOUSING	PA6-GF15	SULFUR YELLOW SIML. RAL 1016	2	
				1	INNER HOUSING	PA66-GF30	BLACK RAL 9011	1	
3-1718643-1	C	CONNECTOR 2POS.	A	1	CPA	PA46-GF15	GREY SIML. RAL 7037	5	
				1	SEAL	MVQ	NATURE -	4	
				1	RETAINER	PA66-GF15	VIOLETT SIML. RAL 4006	3	
				1	OUTER HOUSING	PA6-GF15	BLACK RAL 9011	2	
				1	INNER HOUSING	PA66-GF30	BLUE SIML. RAL 5012	1	
2-1718643-1	B	CONNECTOR 2POS.	E	1	CPA	PA46-GF15	GREY SIML. RAL 7037	5	
				1	SEAL	MVQ	NATURE -	4	
				1	RETAINER	PA66-GF15	VIOLETT SIML. RAL 4006	3	
				1	OUTER HOUSING	PA6-GF15	BLACK RAL 9011	2	
				1	INNER HOUSING	PA66-GF30	NATURE -	1	
1-1718643-1	A	CONNECTOR 2POS.	E	1	CPA	PA46-GF15	GREY SIML. RAL 7037	5	
				1	SEAL	MVQ	NATURE -	4	
				1	RETAINER	PA66-GF15	VIOLETT SIML. RAL 4006	3	
				1	OUTER HOUSING	PA6-GF15	BLACK RAL 9011	2	
				1	INNER HOUSING	PA66-GF30	BLACK RAL 9011	1	
TE. ORDER-NO.		COD	TITLE	REV	QTY	TITLE	MATERIAL	SURFACE/COLOUR	ITEM

[illegible]