






PRODUCT N°
SEE TABLE



SEE NOTE 6



rev	ecn no	dr	date
M	F06-0152	DLE	06.03.20
N	F06-0242	DLE	06.07.20
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - 		tolerance std		projection 	
			ISO 1302		±0.13 ±2°			
TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	D LEGRAND	02.09.16	ANGULAR	LINEAR	D.X	±Y	size A3	Scale 3:1
Eng	P NIZZI	02.09.16			O.XX	±Y	ECN F06-0242	Spec ref -
Chr	D LEGRAND	02.09.16	a° ±Y°		a.XXX	±Y		
Appr	P NIZZI	02.09.16	Product family MODULAR JACK					
			title VERTICAL SMT 6 POSITIONS KEYED			dwg no 98433		Rev. N
			catalog no 98433-XXX(LF)			CUSTOMER		sheet 1 of 2

PRODUCT N°
98433-XXXLF


CONTACT PLATING OPTION	PACKAGE OPTIONS	VERSION
1= GXT 0 76 μ m	TAPE AND REEL PACKAGE 1= LOADED FACE UP	TOP (RED)
3= 0.76 μ m GOLD	TAPE AND REEL PACKAGE 2= LOADED FACE DOWN	BOTTOM (RED)
5= 1.27 μ m GOLD		

TERMINAL LOADING OPTIONS
1= FULLY LOADED 6 POSITIONS
2= ONLY POS 2,3,4,5 LOADED
3= ONLY POS 1,2,5,6 LOADED


WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS RoHS COMPATIBLE SEE NOTE 7.

NOTES:

- NOTES:
- 1 - MATERIAL:
HOUSING: HIGH TEMP. PLASTIC, COLOR RED
TERMINAL PHOSPHOR BRONZE
 - 2 - PLATING
CONTACT AREA: OPTIONAL SEE TABLE
SOLDER TAIL: SnPb 90/10 2 μ m MIN
NO RAW EDGES EXEPT SOLDER TAILS TIPS
 - 3 - AREA FOR VACUUM PICK AND PLACE VENTURY
 - 4 - PACKAGING SPECIFICATION SEE TA 858
 - 5 - DIMENSION MEASURED FROM "A" TO THE TOP OF PRODUCT
 - 6 - COPLANARITY SEE TA 861.
 - 7 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μ m MINIMUM MATTE TIN OVER 1.27 μ m
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY:
 - THE HOUSING WILL WITHSTAND EXPLOSURE TO
245 °C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELLING:
 - MEETS PACKAGING SPECS AS PER GS-14-920.
 - d - LEGAL STATEMENT: SEE GS-22-008



RECOMMENDED PCB FOOTPRINT

www.fciconnect.com			surface -  ISO 1302		tolerance std ±0.13 ±2°		projection 		mm 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	D LEGRAND	02.09.16	ANGULAR		LINEAR		D.X		±Y			
Eng	P NIZZI	02.09.16					0.XX		±Y			
Chr	D LEGRAND	02.09.16	α° ±Y°				0.XXX		±Y			
Appr	P NIZZI	02.09.16	Product family MODULAR JACK						ECN F06-0242			
			Spec ref									
			title VERTICAL SMT 6 POSITIONS KEYED				dwg no 98433				Rev N	
			catalog no 98433-XXX(LF)				CUSTOMER				sheet 2 of 2	