



### FEATURES:

- Maxigrabber® test clip has been redesigned to meet IEC 1010-2-31. This is the latest international safety standard for test accessories.
- The long shaft is ideal for electronic, electrical and industrial applications where access to hard to reach high voltage test points is a requirement.
- The Tip Guard is Stainless Steel for tip durability..
- Safety sheathed jack mates to Pomona's 5907A, 5908A and 5909A Flexible Test Leads for Digital Multi-Meter interfacing.

### MATERIALS:

Hook: Beryllium Copper, Nickel Plated

Plunger, Housing: Polypropylene, Color: One Black, One Red

Banana Jack: Body - Brass, Nickel Plated

Tube: Polypropylene, Color: Yellow

Compression Spring: Stainless Steel

### RATINGS:

IEC 1010, Category III, P2 Compliant

Operating Voltage: 1000 VRMS/DC

Operating Current: 10 Amperes Max.

### ORDERING INFORMATION:

 Model 5911A (Includes Set of one black and one red)

The Maxigrabber® Test Clip is also available in various Pomona DMM Test Kits.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA