



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REV PER ECR 09-027810	29DEC09	JR	TM
	B2	REVISED PER ECO-17-016547	14NOV2017	RS	DR



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
8 AWG SOLID OR STRANDED	8 AWG STRANDED	8 AWG SOLID OR STRANDED

- 1 STAMP AMP 8* APPROX AS SHOWN.
- 2 NOTE DELETED.
- 3 COPPER PER ASTM B-152, ANNEALED.
- 4 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545.



1000	ON TAPE, REEL	55991-2
100	LOOSE PIECE	55991-1
QTY	PACKAGE TYPE	PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F] MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN DK. SCHRUM 19AUG94	TE Connectivity			
		CHK DA PATTERSON 23AUG94				
		APVD JL MECKLEY 23AUG94				
		PRODUCT SPEC UL 486 A-B				
VOLTAGE RATING: N/A	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± - FINISH	NAME TERMINAL, RING TONGUE, SOLISTRAND, 8 AWG			
CIRCULAR MIL AREA: 6.64-10.5mm²[13,100-20,800] SOLID OR STRANDED	MATERIAL 3	4	SIZE A2	CAGE CODE 00779	DRAWING NO C=55991	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV B2	