




174-7123



174-7124



174-7125



### Specifications:

- Type: male
- Housing: zinc high pressure diecast
- Finish: satin nickel or black chrome
- Contacts: silver plated solid brass
- Pin base moldings: noryl (UL94V-1)
- Grommets: santoprene
- Collets: acetal
- Working voltage: 250VDC or AC peak
- Test voltage: 1500VAC
- Contact resistance: 3mΩ max.
- Temperature range: -30°C ~ +80°C

| Mouser Stock No. | No. of Pins | Current Rating | Maximum Wire Gauge |
|------------------|-------------|----------------|--------------------|
| 174-7123         | 3           | 16A            | 12AWG              |
| 174-7124         | 4           | 10A            | 16AWG              |
| 174-7125         | 5           | 7.5A           | 18AWG              |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Deltron:](#)

[709-0500](#) [709-0300](#) [709-0400](#) [713-0400](#)