


C-170359



NOTES:

1. THIS CONTACT IS USED ON EITHER PLUG AND CAP HOUSING.
2. APPLICABLE PRODUCT SPEC : 108-5138
3. APPLICABLE APPLICATION SPEC : 114-5050
4. REFER TO IS-105J FOR APPLICATION FOR MOUNTING TO CONNECTORS.

△ 0.00076 mm MIN. THICK GOLD-PLATED IN THE CONTACT SECTION TO 3.2 mm FROM THE TIP END, OVER NICKEL UNDERPLATE ALL OVER.

注:

1. 使用ハウジングはキャップ及びプラグ
2. 適用製品仕様書 : 108-5138
3. 適用圧着仕様書 : 114-5050
4. 取扱説明書 : JS-105J

△ ホン先端から3.2の間0.76mm最小の金めっき 残部はニッケルめっき。

|                            |                           |
|----------------------------|---------------------------|
| 170361, 170362             | 170363-1, 170359-1        |
| 170365, 170366             |                           |
| 組合相手側型番 (MATING CONN. P/N) | 仕上・材料 (FINISH / MATERIAL) |
| 銅めっき付リン青銅 (TIN/PHOS.BRD)   | 銅めっき△黄銅 (GOLD/BRASS △)    |
| 銅めっき付黄銅 (TIN/BRASS)        |                           |
| 170363-1                   | 170359-1                  |
| は51穴端子型番 (L.P. P/N)        | 型番 (P/N)                  |

参考図面 (CUSTOMER COPY REFERENCE ONLY)

表参照 SEE TABLE 0.2x

表参照 SEE TABLE

WIRE RANGE # 0.12 ~ 0.35 AWG26~22

INSULATION DIA 1.2 ~ 1.75 mm

公差 (TOLERANCE) ±0.4 (EXCEPT AS NOTED) ±0.3

TE

TE Connectivity

GLASS

TYPE

E2 REVISED PER ECO-11-005294

RK

HMR

14APR 11

LTR 変更 REVISION RECORD

DR.

CHK.

DATE

DR. 2. Y. K. 9/1/99

DE

7. T. 9/1/99

CHK. 2. Y. K. 9/1/99

APP.

7. T. 9/1/99

NAME MINI UNIVERSAL MATE-N-LOK PIN CONTACT

ニユニバーサルマテロックピンコネクタ