



KF-E CONNECTORS FOR USE WITH KE UNCOVERED CONDUITS

FIXED MALE CONNECTOR:



CONDUIT SIZE (mm)	THREAD TYPE	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)				
				THREAD DIA.	MIN. BORE	ACROSS FLATS	THREAD LENGTH	NOM. LENGTH
10	Pg to DIN 40430	Pg7	GFP 0101	12.5	4.8	14.0	5.0	16.5
12		Pg9	GFP 0202	15.2	7.8	17.0	8.0	21.5
16		Pg11	GFP 0303	18.6	10.9	20.0	12.0	28.0
20		Pg16	GFP 0405	22.5	14.9	24.0	12.0	28.0
25		Pg21	GFP 0506	28.3	18.9	30.0	13.5	31.0
32		Pg29	GFP 0607	37.0	25.9	40.0	15.0	33.0
40		Pg36	GFP 0708	47.0	33.9	49.6	17.0	36.0
16	Metric to BS 6053	16mm	GFM 0303	16.0	10.8	19.0	10.0	24.5
16		20mm	GFM 0304	20.0	10.8	24.0	10.0	24.5
20		20mm	GFM 0404	20.0	14.8	24.0	10.0	24.5
25		25mm	GFM 0505	25.0	18.8	30.0	12.0	28.0
32		32mm	GFM 0606	32.0	25.8	36.0	13.0	29.0
40		40mm	GFM 0707	40.0	33.8	46.0	15.0	31.5
50		50mm	GFM 0808	50.0	41.8	55.0	15.0	33.0

KF-E SWIVEL MALE CONNECTOR:



CONDUIT SIZE (mm)	THREAD TYPE	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)				
				THREAD DIA.	MIN. BORE	ACROSS FLATS	THREAD LENGTH	NOM. LENGTH
10	Pg to DIN 40430	Pg7	GGP 0101	12.5	4.8	14.0	5.0	22.0
12		Pg9	GGP 0202	15.2	7.8	17.0	8.0	30.3
16		Pg11	GGP 0303	18.6	10.9	20.0	12.0	38.0
20		Pg16	GGP 0405	22.5	14.9	24.0	12.0	38.0
25		Pg21	GGP 0506	28.3	18.9	30.0	12.0	41.0
32		Pg29	GGP 0607	37.0	25.9	40.0	15.0	46.0
40		Pg36	GGP 0708	47.0	33.9	49.6	17.0	51.0
16	Metric to BS 6053	16mm	GGM 0303	16.0	10.8	19.0	10.0	34.3
20		20mm	GGM 0404	20.0	14.8	24.0	10.0	34.3
25		25mm	GGM 0505	25.0	18.8	30.0	12.0	40.5
32		32mm	GGM 0606	32.0	25.8	36.0	13.0	41.5
40		40mm	GGM 0707	40.0	33.8	46.0	15.0	47.3
50		50mm	GGM 0808	50.0	41.8	55.0	15.0	47.0

KF-E SPACE SAVER CONNECTOR:



CONDUIT SIZE (mm)	ORDERING CODE	DIMENSIONS (mm)		
		MIN. BORE	ACROSS FLATS	NOM. LENGTH
10	GYN0101	4.8	14.0	11.5
12	GYN0202	7.8	16.0	13.5
16	GYN0303	10.8	19.0	14.5
20	GYN0404	14.8	24.0	14.5
25	GYN0505	18.8	30.0	16.0
32	GYN0606	25.8	36.0	16.0
40	GYN0707	33.8	46.0	16.0
50	GYN0808	41.8	55.0	18.0

MATERIAL: BRASS / NICKEL PLATED

PROPERTIES:

IP RATING WITH RECOMMENDED CONDUIT

IP 40 (PROTECTED AGAINST SOLID FOREIGN OBJECTS OF 1mm DIAMETER OR GREATER AND NO PROTECTION AGAINST WATER).

OPERATING TEMPERATURE

- 50 TO + 200° C.

FITTING INSTRUCTIONS INCLUDED WITH PRODUCT AND AVAILABLE ON REQUEST – LEAFLET No. 808859

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.