

641-Series Pushbutton Switches



The single or double pole 641-Series represent the most compact offerings of our pushbutton switch line. Rugged metal construction, self cleaning contacts and stiff actuation force (3-3 1/2 lbs. typical) have made these switches ideal for most “foot pedal” type applications. These alternate action switches fit a standard .500” mounting hole, have termination options including solder lug, wire lead and PC, and are popular within the Music Industry and Audio-visual Markets.

Dielectric Strength

UL/CSA: 1000V - live to dead metal parts and opposite polarity.

Electrical Life


25,000 cycles

Mechanical Life

100,000 cycles

Operating Temperature

32°F to 185°F (0°C to +85°C)



64111210

¹
Part Number

1 PART NUMBER: SERIES/POLES/CIRCUITRY/RATING/TERMINATION

Single Pole

2A 250VAC, 5A 125VAC

solder lug	PC term.	wire leads.	
64111210	64111212	64111215	ON-OFF
64111220	64111222	64111225	ON-ON

Double Pole

solder lug	PC term.	wire leads.
64112210	64112212	64112215
64112220	64112222	64112225