

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	10A 125V, 6A 250V AC 1/2 HP 125 / 250V AC
Configured for	20A 14VDC
Contact Resistance	50m ohm Max.
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-25 ^o C ~ 85 ^o C
Switch Function	3P SPST (ON) - OFF Lamp dependent
Lamp Type	LED 12VDC 14V w/resistor

() = Momentary Function

MATERIAL:

Frame: Black, Nylon 66 (94-V2)

Actuator: PC Clear (94-V2), For Color Ref. "X" in
Actuator/LED Color Chart and CW P/N.






LED: For Color Ref. "X" in Actuator/LED Color Chart
and CW P/N.

Terminals: Silver plated, Copper alloy

Waterproof Rubber: Black, Silicone


Printed: None

Waterproof: IP65




Orientation Key

Mounting Hole



Circuit Diagram



Full travel: 4.5mm

ACTUATOR/LED COLOR	X
Amber	A
Green	G
Red	R
Blue	U
White	W

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 6/27/2012

Rev. 0

Unit: mm

Checked By: *G. GULD*

Title:
PUSH BUTTON SWITCH

CW P/N:
GPB527C2B02BX1