






FCIconnect.com

Copyright FCI


PRODUCT NUMBER
SEE NOTE 1



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title			
A	V41186	GIP		8/4/94	angles linear	.XX±.01/.3			INCH/MM	4 ROW R/A STB HEADER			
B	V50270	SAR		3/10/95		.xxx±.005/.13				0 GUIDE PINS, DUPLEX PLATING			
C	V81486	HTB		9/8/98		.0'±2'				scale 1:1			
D	V94353	HTB	11/18/99	dr	G. PETERS	8/10/94			dwg no		sheet 1 of 2		size
E	V00264	JWS	1/27/00	enr	J. AFTON	8/4/94			50782		A3		
F	M06-0255	AGS	7/7/06	chr	J. AFTON	8/12/94							
				appd	S. CLARK	8/12/94							
sheet index		revision sheet		F	F								
				1	2								

form: A3

PRODUCT NUMBER	DIM	LENGTH FORMULAS
SEE NOTE 1	DIM "A"	.100/2.54 x NO. OF COLUMNS + .75/19.1
	DIM "B"	.100/2.54 x NO. OF COLUMNS + .450/11.43
	DIM "C"	.100/2.54 x NO. OF COLUMNS - .100/2.54



NOTES:

- ① PRODUCT NUMBERING CODE:
 50782 - X YYY Z
 TAIL LENGTH(NOTE 6)
 NO. OF POSITIONS(NOTE 2)
 PLATING(NOTE 4)
 BASE NUMBER

- PRODUCT NUMBERING CODE FOR
 SELECT LOAD PART NUMBERS:
 50782 - XYYYY
 SEQUENCE NUMBER
 ALWAYS 'XX'
 BASE NUMBER

- ② THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
 i.e.: 6,7,8,9,.....78,79,80.


- ③ HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
 PIN MATERIAL: PHOS. BRONZE

- ④ PLATING OPTIONS:
 A = 50u" Ni UNDER ALL WITH 30u" Au ON CONTACT AREA SnPb ON PCB INTERFACE AND Au FLASH ON ALL OTHER AREAS.

- ⑤ COMPANY NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.

- ⑥ TAIL LENGTH OPTIONS:
 S = .10 / 2.5

7. FOR DOCUMENTATION MENU, SEE SPEC. BUS-01-057.



RECOMMENDED PCB LAYOUT
 (ALL HOLES LOCATED ON .100/2.54 GRID
 UNLESS OTHERWISE SPECIFIED)

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 1:1 FCI	title
F					angles linear .XX±.01/.3		4 ROW R/A STB HEADER
					0'±2' .xxx±.005/.13		0 GUIDE PINS, DUPLEX PLATING
					.xxxx±.0020/.051		dwg no sheet 2 of 2 size
			dr	G. PETERS	8/10/94		50782 A3
			enr	J. AFTON	8/4/94		
			chr	J. AFTON	8/12/94		
			appd	S. CLARK	8/12/94		type Product Customer Drawing
sheet index	revision sheet						