


Specifications

- **Certifications*:** UL, CSA
- **Dielectric Strength:** 1,000V (minimum)
- **Insulation Resistance:** 100 Megohms (minimum)
- **Base Material:** Phenolic
- **Actuator Material:** Brass/Nickel Plate
- **Bushing Material:** Brass/Nickel Plate

Dimensional Specifications: in. [mm]



.125[3.18] DIA .330[8.38] .187[4.74] .187[4.74]	.075[1.91] DIA .437[11.09] .250[6.35] .250[6.35]	.055[1.40] DIA .394[10.00] .187[4.74] .187[4.74]
SOLDER LUG	.250 TAB (Q.C.)	.187 TAB (Q.C.)
TERMINAL TYPE		
#6-32NC-2 THREAD .141[3.58] .370[9.39] .286[7.26]	6.000[152.40] .500[12.70]	
SCREW (ASSEMBLED)	WIRE LEAD	
.062[1.57] .500[12.70] DIA	.038[9.65] .500[12.70] DIA .125[3.17] DIA	
MOUNTING HOLE	WITH KEYWAY	WITH LOCKING RING

2F A 5 3 - 73 /TABS

SERIES	RATING ¹	TERMINATION/FUNCTION ²
2F SINGLE POLE 6F SINGLE POLE MOMENTARY	5 10A 250VAC 15A 125VAC 3/4HP 120-240VAC 6 3A 250VAC 6A 125VAC 1/4HP 120-240VAC	SOLDER .250TAB LUG (QC) FUNCTION ON-NONE-OFF 3 3/TABS 4 1 (ON)-NONE-OFF 3 3/TABS 4 1 ON-NONE-(OFF) 7 7/TABS 8 6 ON-NONE-ON 3 3/TABS 4 1 ON-NONE-(ON) 3 3/TABS 4 1 ON-OFF-ON 3 3/TABS 4 1 (ON)-OFF-(ON) 3 3/TABS 4 1 ON-OFF-(ON) 7 7/TABS 8 6
CIRCUIT		
A ON-NONE-OFF		
B ON-NONE-ON		
C ON-OFF-ON		

	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
BAT	.406	.343	52	57
	.562	.465	63	68
	.687	.465	73	78
	1.00	.343	A2	A7
	2.00	.465	E3	E8
BALL	.500	.343	22	---

Add the suffix /.187TABS. (ex.) 2FA53-73/.187TABS