

Test adapter - PAI-4-FIX BU - 3032729

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: blue

Your advantages

- ✓ Make contact and latch securely to any point in the function shaft
- ✓ Test adapter for accommodating safety test plugs with a 4 mm diameter



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 280303
GTIN	4046356280303
Weight per Piece (excluding packing)	2.410 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Height	51.5 mm
Length	5.8 mm
Width	5.8 mm
Diameter	5.8 mm
Pin diameter	2.4 mm

General

Test adapter - PAI-4-FIX BU - 3032729

Technical data

General

Note	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
	Do not plug in while the power is connected
	Latching testing accessories, therefore only suitable for being plugged in once
Color	blue

Material	Copper
Ambient temperature (operation)	-40 °C ... 125 °C
Max. voltage	250 V
Maximum load current	10 A
Insertion/withdrawal cycles	1

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27440313
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27440313
eCl@ss 8.0	27440313
eCl@ss 9.0	27440313

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002255
ETIM 6.0	EC002255
ETIM 7.0	EC002255

Test adapter - PAI-4-FIX BU - 3032729

Classifications

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121410
UNSPSC 18.0	39121410
UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU C- DE.BL08.B.00511
-----	---	--------------------------