





***SHOW DREINTINATION OF CAP IN
RESPECT TO E-SWITCH LOGD***



RECOMMENDED P.C.B. LAYOUT

SCALE 2:1



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4; X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: FIXED: SILVER
MOVING: GOLD
5. CONTACT RATING: 250mA @120V DC
6. CONTACT RESISTANCE: 200 MILLI-Ω TYP. INITIAL
7. DIELECTRIC STRENGTH: 1000V for 2min.
8. KEY PRESSURE: 200±50gf
9. PRE-TRAVEL TO MAKE: 1.0mm TYPICAL
10. TRAVEL: 2.5±.3mm
11. MECHANICAL LIFE: 500,000 CYCLES

REV.		ECN No.	DESCRIPTION	DATE	CHKD	SCALE	DATE	DR	DWG	REV
A		11751	RELEASED FOR PRODUCTION	1/23/03	CB	2:1	--	--	XL0144P	A
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED										

E-SWITCH®

4220 DA □ A 5 (Momentary)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[420-OA-0-A-RED XL0144P](#)