


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE	EXPANDED WIRE RANGE**	BARREL		OVERALL LENGTH "A" ± .12	WIRE STRIP LENGTH	PANDUIT CRIMP TOOL PART NUMBERS			
			I.D. ± .01	O.D. ± .01			CT-720	CT-920, CT-920CH, CT-930, CT-930CH, CT-940CH*, CT-2920, CT-2940*	CT-2001	CT-2950*** CT-2980 CT-980 CT-980CH
SCL300-X	300 MCM	#2/0-300 MCM	.650	.813	4.12	2	CD-720-4 WHITE P66 4 CRIMPS	CD-920-300 WHITE P66 3 CRIMPS	CD-2001-300 WHITE P66 3 CRIMPS	STD 3 CRIMPS
SCL350-X	350 MCM	#3/0-350 MCM	.700	.875	4.12	2	CD-720-5 RED P71 4 CRIMPS	CD-920-350 RED P71 3 CRIMPS	CD-2001-350 RED P71 3 CRIMPS	STD 3 CRIMPS
SCL400-6	400 MCM	#4/0-400 MCM	.762	.950	4.37	2-1/8	CD-720-6 BLUE P76 4 CRIMPS	CD-920-400 BLUE P76 3 CRIMPS	CD-2001-400 BLUE P76 4 CRIMPS	STD 3 CRIMPS
SCL500-6	500 MCM	#4/0-500 MCM	.836	1.059	4.62	2-1/4	CD-720-7 BROWN P87 4 CRIMPS	CD-920-500 BROWN P87 3 CRIMPS	CD-2001-500 BROWN P87 4 CRIMPS	STD 3 CRIMPS
SCL600-6	600 MCM	250-600 MCM	.923	1.187	5.50	2-11/16	————	CD-920-600 GREEN P94 4 CRIMPS	————	STD 4 CRIMPS
SCL750-6	750 MCM	500-750 MCM	1.031	1.299	5.87	2-7/8	————	CD-920-750 BLACK P106 4 CRIMPS	————	STD 4 CRIMPS
SCL1000-3	1000 MCM	————	1.173	1.500	6.12	3	————	————	————	————



NOTES:

1. MATERIAL - HIGH CONDUCTIVITY SEAMLESS COPPER TUBING.
2. ELECTRO-TIN PLATED.
3. BARREL COLOR CODED WITH DIE SET INDEX NUMBER.
4. UL LISTED WITH CODE COPPER CONDUCTORS FOR APPLICATIONS UP TO 35 KV, FILE E52164.
5. CONSULT CABLE MANUFACTURER FOR VOLTAGE STRESS RELIEF INSTRUCTIONS WITH APPLICATIONS GREATER THAN 2000 VOLTS.
6. CSA CERTIFIED FOR APPLICATIONS UP TO 600 V, FILE LR31212.
7. FOR USE WITH COPPER CABLES ONLY.

* CD-920 DIES CAN BE USED WITH CT-940CH AND
CT-2940 TOOLS WITH CD-940-DA ADAPTER
** WITH CT-980, CT-980CH, CT-2950 & CT-2980
*** MAX SIZE 500 MCM



LISTED
587H
E52164



CERTIFIED
LR31212

										C41132_03	
										PANDUIT CORP TINLEY PARK, ILLINOIS	
										SCL STANDARD BARREL #300 THRU 1000 COPPER SPLICES	
03	4/01	BOK	ADDED THE LETTER "P" TO THE DIE INDEX NUMBER. ADDED CT-2950, CT-2980, CT-980 & CT-980CH. CHANGED NUMBER WHO WITH CT-940-DA ADAPTER. ALTERNATE DIE INDEX NUMBER NOTE. REVISED UL/CSA LOGOS. ADDED EXPANDED WIRE RANGE.							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: 1.X1 ± 1.00X1 ± 1.00X1 ±	
02	3.94	WB	ADDITIONAL NOTES ADDED.							UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION	
01	11-93	PWS	FILESPEC WAS C41106 & DWG WAS C41106							SCALE	N/A
00	3-93	PWS GRM	RELEASED							DRAWING NO.	C41132
REV	DATE	BY	CHK	DESCRIPTION						ECN	PM