


SPECIFICATION SHEET



Capacitance:	150 pF
M Tolerance:	+/-20%
DF:	< 2.5% @ 1kHz
IR:	> 10 ¹⁰ Ω
Work Voltage:	25 VDC
TC:	+/-15% (@ -55/+125C)
Metallization:	
Top:	TiW / Pt / Au (100μ" min)
Bottom:	TiW / Pt / Au (100μ" min)
Dimension:	15 +/- 5 x 15 +/- 5 x 6 +/- 1 mils
RoHS:	Compliant (Lead Free)

NOTES

PREPARED BY: Cathy Hung	DESCRIPTION: SINGLE LAYER CHIP CAPACITOR	REV.:
		SCALE: Not to Scale
DATE: 10/19/09	TECDIA PART NUMBER: SK01C151M11A6	SHEET: 1 of 1