

3M

Volition™

RJ45 K6 Jack

The 3M™ Volition™ K6 jack is a unique and simple Cat. 6 hardware component (TIA/EIA-568 B.2 and ISO/IEC 11801 2nd Edition), utilizing the universally accepted keystone mounting. It offers a quick and reliable Cat. 6 connection as the eight copper conductors are effortlessly terminated in a single operation without tools.

The K6 jack is the core product of 3M's Cat. 6 copper structured cabling solution, offering superior performance over Cat. 6 link standards.

Features

- Category 6 hardware component, 3rd party (Delta) verified to TIA/EIA-568 B.2 Cat. 6
- Tool-less connector
- Keystone mounting
- ISO 8877 compliant
- Integral shutter
- Top or bottom cable insertion
- Self-stripping contacts with 1.3µm gold plating
- Either TS68A or TS68B wiring scheme
- UL listed



A Unique Design

Tool-less jack:

- Easy and quick to install
- Fast reliable connection in record time: all eight copper conductors are effortlessly wired in a single operation
- Quality of connection by design: not dependent on tool condition or operator skills; just listen for the click
- Consistent results: the length of untwisted pairs is always kept to a minimum, by design

Re-usable:

- If a wiring mistake is made, there is no need to use a new jack
- No time wasted waiting for another delivery

Shallow depth, cable entry from top or bottom:

- Easier cable management
- More space and flexibility to ensure the cable minimum bend radius is never compromised
 - Allows a wide range of cable routing options
 - Can be used with low profile trunking and boxes

Keystone mounting:

- Compatibility between Volition copper and fiber jacks and many other accessories on the market using standard keystone mounting

Accepts both solid conductors from AWG 26 to 22 and stranded conductors:

- Compatible with all cables on the market and enables "jack to plug" cables to be manufactured using stranded conductors (for use in open office architectures)

Integral shutter:


- Increased dust protection, especially during installation or in a dirty environment
- No additional shuttering required on faceplates
- Allows direct mounting into floor boxes
- Protects jacks in the patch panel

Technical Characteristics

RJ45 Category 6 Hardware test result (worst case)

Frequency	100 MHz	200 MHz	250 MHz
Attenuation	< 0.2 dB	< 0.2 dB	< 0.3 dB
Return Loss	24 dB	18.5 dB	16 dB
NEXT Pair to Pair	58 dB	50 dB	47.5 dB
Ø of the conductors	AWG 26 to 22		
Ø of the sheath	1.60 mm maximum		
Insulation resistance	> 10 MΩ		

Dimensions: 23 x 18 x 35 mm (0.9 x 0.7 x 1.4 in.)



Ordering Information

Model Number	Description	Minimum Order Quantity	Packaging
VOL-OCK6-U-W	RJ45 K6 Jack UTP, white	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-BU	RJ45 K6 Jack UTP, blue	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-G	RJ45 K6 Jack UTP, green	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-R	RJ45 K6 Jack UTP, red	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-Y	RJ45 K6 Jack UTP, yellow	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-BL	RJ45 K6 Jack UTP, black	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-O	RJ45 K6 Jack UTP, orange	1 carton	Carton of 96 (12 bags of 8)
VOL-OCK6-U-AL	RJ45 K6 Jack UTP, almond	1 carton	Carton of 96 (12 bags of 8)

3M and Volition are trademarks of 3M.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one year from the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



Telecom Enterprise Department
3M Telecommunications

6801 River Place Blvd.
Austin, TX 78726-9000
800-695-0447
FAX 800-626-0329
www.3MTelecommunications.com



Minimum 10%
Post-consumer Fiber

Printed in USA.

© 3M Company 2003 80-6111-3184-0