

## 18x16x8 Inch Weatherproof Enclosure with Blank Aluminum Mounting Plate

### Model: NB181608-KIT

#### Applications and Features

**Features:**

- Molded Fiberglass Reinforced Polyester (FRP) industrial Enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 4, 4X / IP66 rated
- Fully gasketed raised lid & integral mounting flange
- Includes blank, aluminum mounting plate

**Applications:**

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage



## Product Description

---

### Start with the Box...

The box is a rugged 18" x 16" x 8" weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass, it is well suited for high temperature or corrosive environments. The mounting flange allows it to be wall mounted as well as on a flat surface. The box can also be pole mounted with the optional pole mounting hardware kit. The fully gasketed lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The enclosure material is UV stabilized and comes in machine tool gray.

This model features a .10 thick blank aluminum mounting plate inside the enclosure.

The NB181608-KIT is ideal for custom applications, which may require special modifications to the enclosure.

## Specifications

---

<b>Enclosure Material</b>	Fiberglass Reinforced Polyester
<b>Enclosure Color</b>	Machine Tool Gray
<b>Mounting Plate Material</b>	.10 in. (2.5mm) Thick Anodized Aluminum
<b>Mounting Plate Dimensions</b>	16.8 x 14.8 inches (42.6 x 37.5 cm)
<b>Weight</b>	19.3 lbs (8.8 kg)
<b>Outside Dimensions (max)</b>	19.5 x 17.5 x 9 inches (49.5 x 44.4 x 22.8 cm)
<b>Inside Dimensions</b>	17.7 x 15.7 x 8.5 inches (44.9 x 39.9 x 21.6 cm)
<b>Flame Rating</b>	UL 94-5V
<b>RoHS Compliant</b>	Yes
<b>Ratings</b>	NEMA 4, 4X / IP66

**Enclosure Dimensions**

