



Sample photo

Order symbol: PC 100/100 LT
Product nbr: 6012904
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022271
El. number:
Finland: 3420415
Denmark: 8212022328
Italy: 7352020
Sweden: 2535609
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Rating:
mm:	130	80	Ingress Protection (EN 60529): IP 66/67
inch:	5.1	3.1	Impact Resistance (EN 62262): IK 08
Materials:			Electrical insulation: Totally insulated
Material:	Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035		UV resistance: UL 508
Cover colour:	Smoked grey		Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:	Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Black		NEMA Class: NEMA 1, 4, 4X, 6
Gasket material:	TPE		
Temperatures:			Certificates:
Short term:	-40 ... 120 °C		Germanischer Lloyd (GL)
Continuous:	-40 ... 80 °C		Underwriters Laboratories
Short term:	-40 ... 250 °F		Det Norske Veritas
Continuous:	-40 ... 175 °F		Fimko
Accessories:			Europe EN 62208: 2003
MIV 100	Mounting plate (Galvanized steel)		UL Canada
MIN 5	DIN-15 Mounting rail		Gost R
MIN 10	DIN-15 Mounting rail		
MIV 5	DIN-35 Mounting rail		
MIV 10	DIN-35 Mounting rail		
FP A 100/130	Front plate (Aluminium)		
HFP 130	Front plate hinge series		
FP 22046	Wall fastening lug (4 pcs)		

