




OBSOLETE 6	3.984	3.900	39	40	2-104345-7
	3.484	3.400	34	35	2-104345-6
	2.984	2.900	29	30	2-104345-5
	2.584	2.500	25	26	2-104345-4
	2.484	2.400	24	25	2-104345-3
	2.384	2.300	23	24	2-104345-2
	2.284	2.200	22	23	2-104345-1
	2.184	2.100	21	22	2-104345-0
	2.084	2.000	20	21	1-104345-9
	1.984	1.900	19	20	1-104345-8
	1.884	1.800	18	19	1-104345-7
	1.784	1.700	17	18	1-104345-6
	1.684	1.600	16	17	1-104345-5
	1.584	1.500	15	16	1-104345-4
	1.484	1.400	14	15	1-104345-3
OBSOLETE 6	1.384	1.300	13	14	1-104345-2
	1.284	1.200	12	13	1-104345-1
	1.184	1.100	11	12	1-104345-0
	1.084	1.000	10	11	104345-9
	.984	.900	9	10	104345-8
6 OBSOLETE	.884	.800	8	9	104345-7
	.784	.700	7	8	104345-6
	.684	.600	6	7	104345-5
	.584	.500	5	6	104345-4
	.484	.400	4	5	104345-3
	.384	.300	3	4	104345-2
	.284	.200	2	3	104345-1
	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN H. MOLL		08FEB88		 TE Connectivity							
			CHK R. FEIDT		08FEB88									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. FEIDT		08FEB88		NAME						
INCHES				PRODUCT SPEC		HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 CL, VERT, .025 SQ POSTS, WITH RETENTION FEATURE								
		1 PLC ± —		—										
		2 PLC ± —		APPLICATION SPEC										
		3 PLC ± .005		—										
		4 PLC ± —		—										
ANGLES		± —		WEIGHT		—		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POST: COPPER ALLOY		FINISH: POST: .000015 GOLD IN CONTACT AREA, .000100—.000200 MATTE TIN—LEAD OR SOLDER TAIL, ALL OVER .000050 NICKEL				A2		00779		C-104345		—		
CUSTOMER DRAWING						SCALE		4:1		SHEET		1 of 1	REV	K