

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190190036

Status:

Active

Description:


Avikrimp™ Quick Disconnect, Female, for 14-16 (2.00-1.30) Wire, Metal Strip, Tab 6.35mm (.250") x 0.81mm (.032")

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Quick Disconnects
Series	19019
Product Name	Avikrimp™
Type	Quick Disconnect
Physical	
Barrel Type	Closed
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.81mm (.032")
Tab Width	6.35mm (.250")
Temperature Range - Operating	-65°C to +105°C
Wire Insulation Diameter	3.50mm (.138") max.
Wire Size AWG	14
Wire Size AWG	16
Wire Size mm²	1.30 - 2.00
Electrical	
CSA	LR18689
UL	E79133
Voltage - Maximum	300V
Material Info	
Old Part Number	BBZ-8141
Reference - Drawing Numbers	
Sales Drawing	CD81205



Series image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Halogen-Free Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19019 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
ASP Tool Kit, Perishable, Used in an ASP-200 Press that Processes Metal Strip Product	0192870093
Mini-Mac™ Applicator	0638810900

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION