

## 507 SERIES CARTRIDGES FOR USE WITH HOLDERS & CLIPS

| PART NO.*          | COLOR | V <sub>F</sub> | mA  | CP   | LIFE HOURS | FIG |
|--------------------|-------|----------------|-----|------|------------|-----|
| 507-3911-1431-600  | RED   | 10             | 40  | 0.08 | 10,000     | 1   |
| 507-3911-1432-600  | GREEN | 10             | 40  | 0.08 | 10,000     | 1   |
| 507-3911-1433-600  | AMBER | 10             | 40  | 0.08 | 10,000     | 1   |
| 507-3911-1435-600  | WHITE | 10             | 40  | 0.08 | 10,000     | 1   |
| 507-3914-1471-600  | RED   | 14             | 80  | 0.30 | 15,000     | 1   |
| 507-3914-1472-600  | GREEN | 14             | 80  | 0.30 | 15,000     | 1   |
| 507-3914-1473-600  | AMBER | 14             | 80  | 0.30 | 15,000     | 1   |
| 507-3914-1475-600  | WHITE | 14             | 80  | 0.30 | 15,000     | 1   |
| 507-3917-1471-600  | RED   | 28             | 40  | 0.34 | 4,000      | 1   |
| 507-3917-1472-600  | GREEN | 28             | 40  | 0.34 | 4,000      | 1   |
| 507-3917-1473-600  | AMBER | 28             | 40  | 0.34 | 4,000      | 1   |
| 507-3917-1475-600  | WHITE | 28             | 40  | 0.34 | 4,000      | 1   |
| 507-3918-1437-600  | CLEAR | 28             | 40  | 0.30 | 7,000      | 1   |
| 507-3918-1471-600  | RED   | 28             | 40  | 0.30 | 7,000      | 1   |
| 507-3918-1472-600  | GREEN | 28             | 40  | 0.30 | 7,000      | 1   |
| 507-3918-1473-600  | AMBER | 28             | 40  | 0.30 | 7,000      | 1   |
| 507-3918-1475-600  | WHITE | 28             | 40  | 0.30 | 7,000      | 1   |
| 507-5820-0747-600† | CLEAR | 12             | 170 | 2.10 | 5,000      | 3   |
| 507-5821-0747-600† | CLEAR | 28             | 40  | 1.20 | 5,000      | 3   |
| 507-5822-0747-600† | CLEAR | 48             | 53  | 1.50 | 5,000      | 3   |
| 507-5824-0747-600† | CLEAR | 120            | 25  | 1.50 | 5,000      | 3   |

† Use Holder 250-8758-33-504 and 250 Series Cap

Fig. 1




Fig. 2





Fig. 3



**\*PART NUMBER ORDERING CODE**

**507 - 39xx - xxxx - 600**

Series


Lens Shape:

14 - Fig 1 = Cylindrical

09 - Fig 2 = Stovepipe


## 250 & 508 SERIES HOLDERS FOR 3/8" MOUNTING HOLE

HOLDER WITHOUT COLLAR\*




250-8738-14-504

HOLDER WITH COLLAR \*



508-8738-504

HOLDER WITHOUT COLLAR†




250-8758-33-504  
for Figure 3 Only

250 Series Caps for use with 507 cartridges.

| CAP PART NO. | COLOR | FIG |
|--------------|-------|-----|
| 250-3531-500 | RED   | 4   |
| 250-3532-500 | GREEN | 4   |
| 250-3533-500 | AMBER | 4   |
| 250-3535-500 | WHITE | 4   |
| 250-3537-500 | CLEAR | 4   |

Fig. 4



**\*PART NUMBER ORDERING CODE**

**250 - xx38 - 14 - 504**

**508 - xx38 - 504**

Series

Terminal Type:


87 = Turret Terminals

74 = Solder Blade (Not Shown)


75 = Solder Cups (Not Shown)

Material & Finish: Holder – Black Anodized Aluminum, Cap – Polycarbonate, Cartridge Clear Anodized Aluminum


## 515 SERIES CONNECTORS & SPEED CLIPS FOR 9/32" MOUNTING HOLE




CONNECTOR  
515-0012



CONNECTOR  
515-0074



SPEED CLIP 515-0051



Dimensions in mm [inches]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Dialight:

[250-8758-33-504](#) [250-7538-14-504](#) [250-3537-500](#) [250-3532-500](#) [250-3535-500](#) [250-3533-500](#) [250-8738-14-504](#)  
[250-3531-500](#) [250-7438-14-504](#) [507-3911-1471-600F](#) [507-3944-0971-600F](#) [507-3914-0973-600F](#) [507-3909-0935-600F](#) [507-3911-1435-600F](#) [507-3916-1472-600F](#) [507-3904-1432-600F](#) [507-3909-0972-600F](#) [507-3916-1475-600F](#)  
[507-3909-0975-600F](#) [507-3914-1476-600F](#) [507-3914-1433-600F](#) [507-3913-1471-600F](#) [507-3917-0937-600F](#) [507-3914-0937-600F](#) [507-3917-1434-600F](#) [507-3913-1475-600F](#) [507-3906-1473-600F](#) [507-3913-0975-600F](#) [507-3909-0973-600F](#) [507-3916-1473-600F](#) [507-3910-1432-500F](#) [507-3911-1433-600F](#) [507-3909-0932-600F](#) [507-3910-1433-600F](#) [507-3913-1475-600](#) [507-3905-1471-600F](#) [507-3914-0971-600F](#) [507-3911-1432-600F](#) [507-3917-0976-600F](#) [507-3913-1472-600F](#) [507-3906-1474-600F](#) [507-3918-0974-600F](#) [507-3910-1434-600F](#) [507-3909-1476-600F](#) [507-3904-1437-600F](#) [507-3914-0975-600F](#) [507-3903-1471-600F](#) [507-3917-0935-600F](#) [507-3904-1433-600F](#) [507-3944-1431-600F](#) [507-3906-1437-600F](#) [507-3917-0933-600F](#) [507-3918-1432-500F](#) [507-3917-0972-600F](#) [507-3910-1437-600F](#) [507-3918-1431-500F](#) [507-3913-0971-600F](#) [507-3917-1476-600F](#) [507-3913-1433-600F](#) [507-3910-1431-600F](#) [507-3911-1431-600F](#) [507-3911-1431-600](#) [507-3904-1431-600F](#) [507-3905-1473-600F](#) [507-3913-1476-600F](#) [507-3905-1475-600F](#) [507-3913-1435-600F](#) [507-3914-0972-600F](#) [507-3916-1471-600F](#) [507-3909-1474-600F](#) [507-3944-1471-600F](#) [507-3914-1435-600F](#) [507-3904-1434-600F](#) [507-3903-1472-600F](#) [507-3944-1472-600F](#) [507-3918-1431-600F](#) [507-3914-0931-600F](#) [507-3913-1434-600F](#) [507-3909-1473-600F](#) [507-3910-1432-600F](#) [507-3911-1435-600](#)