

50" Class Viera® G25 Series 1080p Plasma

Model number: TC-P50G25

15 Reviews

Print this | Share this

Product no longer available for purchase.

50" Class Viera® G25 Series 1080p Plasma (49.9" Diagonal)

- VIERA Cast-WiFi w/ VideoPhone Capabilities
- Infinite Black Panel
- VIERA Image Viewer™
- ENERGY STAR Qualified

Online Order Assistance

- [Track your order](#)
- [Print your invoice](#)
- [Read our shipping FAQs](#)
- [Register your product](#)

Accessories

- [Find accessories for your product](#)

Contact Us

- [Live Chat](#)
- [Phone](#)
- [Email](#)
- [Mail](#)
- [International Support](#)

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Drivers & Downloads
Model Type				Plasma	
Series				G25	
Model Year				2010	
VIDEO					
Screen Size				50" Class (49.9" diagonal)	
Contrast Ratio				Infinite Black Panel /5,000,000:1 Native	
Aspect Ratio				16:9	
Native Resolution (Number of Pixels)				2,073,600 (1,920 x 1,080)	
Moving Picture Resolution				1080 lines	
Shades of Gradation				6,144 equivalent	
HDTV Display Capability (1080p, 1080i, 720p)				Yes	
EDTV Display Capability (480p)				Yes	
Aspect Control				Normal, Zoom, Full, Just, H-fill for TV/AV modes 4:3, Full for PC mode	
Full HD 3D				No	
AR (Anti-Reflective) Filter				Yes	
600Hz Sub-field Drive				Yes	
24p Cinematic Playback				No	
24p Playback(2:3)				Yes	
Deep Color				Yes	
x.v.Color				Yes	
Studio Ref Mode				No	
Pro Setting				Yes	
THX Mode				Yes	
ISFccc				No	
3D Color Management				Yes	
Sub Pixel Control				Yes	
Motion Pattern Noise Reduction				Yes	
600 Hz Sub-field Drive				Yes	
AUDIO					
Speakers				Full-range x 2 (L, R)	
Number of Speakers				2	
Audio Output				20 W (10% THD)	
BBE® VIVA HD3D Sound				No	
Surround Sound				Yes	
INPUTS & JACKS					
Integrated ATSC Tuner				Yes	
VIERA Image Viewer™				Y (AVCHD/MPEG2/JPEG Playback)	
HDMI Input				3 (1 side)	
Composite Video Input				2 (1 side)	
Audio Input (for Video)				2 (1 side)	
PC Input				Mini D-sub 15-pin x 1 (side)	
Component Video Inputs (Y, PB, PR)				2	
Audio Input (for Component Video)				2	
RS232C				No	
Digital Audio Output				1	
HDMI Input-Support Feature				Audio Return Channel (Input 1)	
Analog Audio Input (for HDMI/DVI)				Yes	
USB				Yes	
LAN Port				1	
CONVENIENCE					
VIERA Link™				Y (with Network Camera)	
VIERA Cast™ (IPTV)				Yes	
Skype Ready				Yes	
VIERA® Tools				Yes	
Game Mode				Yes	
3D Active Shutter Eyewear				No	
Clean Touch Bezel				No	
Pixel Orbiter (Anti-Image Retention)				Yes	
Built-In Closed Caption Decoder				Yes	
Off - Timers				Yes	
Trilingual Menu				English/Spanish/French	
GENERAL					
Power Supply				AC 120 V, 60Hz	
Energy Star				Yes	
Receiving System				ATSC/QAM/NTSC	
Operating Temperature				32°F - 104°F (0°C - 40°C)	
Safety Standard				UL6500/C-UL	
Swivel Angle				+10°	
Optional Wall-mounting Bracket				TY-WK4P1RW	
SPECIFICATIONS					
.					
Dimensions (H x W x D) with Stand				31.9" x 48.0" x 13.2"	
Dimensions (H x W x D) without Stand				30.3" x 48.0" x 3.5"	
Weight (lbs.) w/Stand				63.9 lbs.	
Weight (lbs.) without Stand				57.3 lbs	
Carton Dimensions				34.4" x 53.0" x 11.2"	
Gross Weight [lbs (kg)]				79.4 lbs. (36 kg)	
Weight				79.4 lbs	