



Wiha Combination Wrenches



400 Combination Wrenches Metric DIN 3113A/ISO 3318 - ISO 7738

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.	O _{MM}	OAL	OAL	H ¹	H ²	D ¹	D ²	lbs.	pkg.
400 01	5.5	100	3.9	5.0	3.0	10.1	15.7	.03	10
400 02	6.0	100	3.9	5.0	3.9	10.1	15.7	.03	10
400 03	7.0	110	4.3	5.5	4.2	11.5	17.0	.04	10
400 04	8.0	120	4.7	5.9	4.4	12.9	19.0	.05	10
400 05	9.0	130	5.1	6.4	4.7	14.5	20.9	.07	10
400 06	10.0	140	5.5	6.9	5.0	15.9	22.8	.09	10
400 07	11.0	150	5.9	7.4	5.2	17.3	25.4	.11	10
400 08	12.0	160	6.3	7.9	5.5	18.7	26.7	.13	10
400 09	13.0	170	6.7	8.4	5.8	20.2	29.3	.14	10
400 11	14.0	180	7.1	8.9	6.1	21.6	31.2	.19	10
400 12	15.0	190	7.5	9.3	6.3	23.1	33.0	.21	10
400 13	16.0	200	7.8	9.8	6.6	24.6	34.5	.23	10
400 14	17.0	210	8.2	10.3	6.9	25.4	37.3	.30	10
400 15	18.0	220	8.6	10.8	7.1	27.4	38.4	.32	10
400 16	19.0	230	9.0	11.1	7.3	28.8	40.4	.34	10
400 17	20.0	240	9.4	11.4	7.5	30.2	42.3	.39	1
400 18	21.0	250	9.8	11.7	7.7	31.7	44.2	.44	1
400 19	22.0	260	10.2	12.0	7.9	33.0	46.6	.51	1
400 20	23.0	270	10.6	12.4	8.1	34.5	48.8	.56	1
400 27	24.0	280	11.0	12.7	8.3	35.8	50.1	.62	1
400 28	25.0	290	11.4	13.0	8.5	37.3	52.8	.66	1
400 29	26.0	300	11.8	13.3	8.7	38.7	53.9	.74	1
400 30	27.0	310	12.2	13.6	8.9	40.2	55.9	.83	1
400 31	28.0	320	12.5	13.9	9.1	41.5	57.8	.88	1
400 32	29.0	330	12.9	14.2	9.3	42.8	59.8	.97	1
400 33	30.0	340	13.3	14.6	9.5	44.3	62.6	1.08	1
400 34	32.0	360	14.1	15.2	9.9	47.2	66.9	1.30	1
400 35	34.0	380	14.9	15.8	10.3	50.1	69.5	1.50	1
400 36	36.0	400	15.7	22.8	14.1	54.6	77.5	2.40	1
400 37	38.0	400	15.7	22.8	14.1	54.6	77.5	2.35	1
400 38	41.0	450	17.6	25.8	15.8	62.1	83.7	3.19	1
400 39	46.0	500	19.6	28.8	17.5	69.6	93.1	4.31	1
400 40	50.0	540	21.1	31.2	18.9	75.6	102.6	5.72	1

400 87 Set 15 Piece Metric Combination Wrenches Made from 31CRV3 high performance tool steel. Satin chromed sure grip body.

Precision formed for exact fit. In roll up pouch

Item No.	OAL	OAL
	mm	mm
400 87	400 04	8.0 120
	400 05	9.0 130
	400 06	10.0 140
	400 07	11.0 150
lbs.	400 08	12.0 160
6.75	400 09	13.0 170
	400 11	14.0 180
	400 12	15.0 190
	400 13	16.0 200
	400 14	17.0 210
	400 15	18.0 220
	400 16	19.0 230
	400 17	20.0 240
	400 19	22.0 260
	400 27	24.0 280



400 92 Set 26 Piece Metric Combination Wrenches In tool box

Item No.	OAL	OAL
	mm	mm
400 92	400 02	6.0 100
	400 03	7.0 110
	400 04	8.0 120
	400 05	9.0 130
	400 06	10.0 140
	400 07	11.0 150
	400 08	12.0 160
	400 09	13.0 170
	400 11	14.0 180
lbs.	400 12	15.0 190
15.3	400 13	16.0 200
	400 14	17.0 210
	400 15	18.0 220
	400 16	19.0 230
	400 17	20.0 240
	400 18	21.0 250
	400 19	22.0 260
	400 20	23.0 270
	400 27	24.0 280
	400 28	25.0 290
	400 29	26.0 300
	400 30	27.0 310
	400 31	28.0 320
	400 32	29.0 330
	400 33	30.0 340
	400 34	32.0 360