




CABLE RANGE PG7
ø2,5 - ø6,5mm

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PA	BLACK
2	HOUSING	PA	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	PG NUT	PA	BLACK
5	O-RING	VITON	RED
6	GROMMET	CR	BLACK
7	ULTRA-LOCK	BRASS /ST.STEEL	NICKEL PLATED

POL	MATERIAL NO.	ENGINEERING NO.
4	1200850011	WA4000-31
5	1200850012	WA5000-31

VOLTAGE RATING: 250 VAC/VDC
AMPERAGE RATING: 4A
PROTECTION CLASS: IP 67/68/69K
OPERATING TEMPERATURE: -25°C / 90°C
UL CERTIFICATION: FILE NO. E152210
CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0320 DRWN:NSTAUDIGEL 2010/02/02 CHKD: 2010/02/05 APPR:FPACHER 2010/02/05 REV 1		DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
					mm	INCH	DRAWN BY NSTAUDIGEL	DATE 2010/02/02	TITLE M12U FA FEM STR PG7				
							CHECKED BY	DATE					
							APPROVED BY FPACHER	DATE 2010/02/05	MOLEX INCORPORATED				
							MATERIAL NO.	DOCUMENT NO. SD-120085-004					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									