

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TABLE 1

P/N	COLOR	LEGENDS (each)	"A" WIDTH +/- .062	MARKER PER CARD	STD. PKG. CARDS QTY.
PCM-0 thru PCM-99	WHITE	'0' thru '99' [1 ea.]	.25 [6.35]	36	25
PCM-100 thru PCM-202	WHITE	'100' thru '202' [1 ea.]	.36 [9.15]	25	25
PCM-A thru PCM-Z	WHITE	'A' thru 'Z' [1 ea.]	.25 [6.35]	36	25
PCM-A1 thru PCM-A4	WHITE	'A1', 'A2', 'A3', 'A4' [1 ea.]	.25 [6.35]	36	25
PCM-B1 thru PCM-B5	WHITE	'B1', 'B2', 'B3', 'B4', 'B5' [1 ea.]	.25 [6.35]	36	25
PCM-C1 thru PCM-C4	WHITE	'C1', 'C2', 'C3', 'C4' [1 ea.]	.25 [6.35]	36	25
PCM-E1 thru PCM-E3	WHITE	'E1', 'E2', 'E3' [1 ea.]	.25 [6.35]	36	25
PCM-F1 thru PCM-F4	WHITE	'F1', 'F2', 'F3', 'F4' [1 ea.]	.25 [6.35]	36	25
PCM-H1 thru PCM-H5	WHITE	'H1', 'H2', 'H3', 'H4', 'H5' [1 ea.]	.25 [6.35]	36	25
PCM-L1 thru PCM-L5	WHITE	'L1', 'L2', 'L3', 'L4', 'L5' [1 ea.]	.25 [6.35]	36	25
PCM-M1, PCM-M2	WHITE	'M1', 'M2' [1 ea.]	.25 [6.35]	36	25
PCM-P1 thru PCM-P3	WHITE	'P1', 'P2', 'P3' [1 ea.]	.25 [6.35]	36	25
PCM-R1 thru PCM-R5	WHITE	'R1', 'R2', 'R3', 'R4', 'R5' [1 ea.]	.25 [6.35]	36	25
PCM-S1 thru PCM-S5	WHITE	'S1', 'S2', 'S3', 'S4', 'S5' [1 ea.]	.25 [6.35]	36	25
PCM-T1 thru PCM-T9	WHITE	'T1', 'T2', 'T3', 'T4', 'T5', 'T6', 'T7', 'T8', 'T9' [1 ea.]	.25 [6.35]	36	25

TABLE 2


P/N	COLOR	LEGENDS (each)	"A" WIDTH +/- .062	MARKER PER CARD	STD. PKG. CARDS QTY.
PCM-X1 thru PCM-X4	WHITE	'X1', 'X2', 'X3', 'X4' [1 ea.]	.25 [6.35]	36	25
PCM-1L1 thru PCM-1L3	WHITE	'1L1', '1L2', '1L3' [1 ea.]	.36 [9.15]	25	25
PCM-2L1 thru PCM-2L3	WHITE	'2L1', '2L2', '2L3' [1 ea.]	.36 [9.15]	25	25
PCM-3L1 thru PCM-3L3	WHITE	'3L1', '3L2', '3L3' [1 ea.]	.36 [9.15]	25	25
PCM-4L1 thru PCM-4L3	WHITE	'4L1', '4L2', '4L3' [1 ea.]	.36 [9.15]	25	25
PCM-1T1 thru PCM-1T3	WHITE	'1T1', '1T2', '1T3' [1 ea.]	.36 [9.15]	25	25
PCM-3T1 thru PCM-3T3	WHITE	'3T1', '3T2', '3T3' [1 ea.]	.36 [9.15]	25	25

NOTES:

1. MILLIMETER ARE IN ().
2. CHARACTERS TO BE UNDERLINE:
99, 66, 9, 6,
86, 89, 68, 98, 16,
19, 61, 91, 60 and 90.

BLUE BOARD

BUTT CUT, TYP.



REV						DESCRIPTION		ECN	TITLE				
									SOLID NUMBERS AND LETTERS PCM-* WIRE MARKER CARDS				
									CUSTOMER DRAWING				
									ITEM REVISION NAME				
									100295CA/07				
									DATASET FILE NAME				
									100295CA_DC_C10796/07F				
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				
									.x ± .12 [3.05] .xxx ± .025 [1.635] .xx ± .062 [1.57] ANGLES ±				
									THIRD ANGLE PROJECTION				
									DRAWN BY				
									RVU				
									DATE				
									10/14/09				
									CHK				
									JHAC				
									SCALE				
									NTS				
									SHT 1 OF 1				
									SIZE				
									A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCM-16](#) [PCM-44](#) [PCM-55](#) [PCM-10](#) [PCM-32](#) [PCM-A3](#) [PCM-13](#) [PCM-15](#) [PCM-66](#) [PCM-11](#) [PCM-19](#) [PCM-28](#)
[PCM-14](#) [PCM-12](#) [PCM-29](#) [PCM-22](#) [PCM-5](#) [PCM-9](#) [PCM-6](#) [PCM-3](#) [PCM-7](#) [PCM-1](#) [PCM-8](#) [PCM-2](#) [PCM-4](#) [PCM-](#)
[30](#) [PCM-31](#) [PCM-33](#) [PCM-49](#) [PCM-25](#) [PCM-110](#) [PCM-116](#) [PCM-B](#) [PCM-C](#) [PCM-G](#) [PCM-L2](#) [PCM-U](#) [PCM-V](#)
[PCM-W](#) [PCM-18](#) [PCM-180](#) [PCM-20](#) [PCM-21](#) [PCM-23](#) [PCM-39](#) [PCM-40](#) [PCM-50](#) [PCM-64](#) [PCM-70](#) [PCM-72](#)
[PCM-84](#) [PCM-87](#) [PCM-I](#) [PCM-L](#) [PCM-N](#) [PCM-F](#) [PCM-O](#) [PCM-A2](#) [PCM-L3](#) [PCM-M](#) [PCM-A1](#) [PCM-D](#) [PCM-26](#)
[PCM-27](#) [PCM-17](#) [PCM-24](#) [PCM-38](#) [PCM-47](#) [PCM-52](#) [PCM-75](#) [PCM-S](#) [PCM-T](#) [PCM-2L1](#) [PCM-43](#) [PCM-61](#)
[PCM-56](#) [PCM-97](#) [PCM-132](#) [PCM-76](#) [PCM-173](#) [PCM-P1](#) [PCM-K](#) [PCM-Z](#) [PCM-1T3](#) [PCM-S5](#) [PCM-41](#) [PCM-152](#)
[PCM-A4](#) [PCM-F1](#) [PCM-3T2](#) [PCM-X4](#) [PCM-94](#) [PCM-168](#) [PCM-73](#) [PCM-T1](#) [PCM-1L3](#) [PCM-79](#) [PCM-59](#) [PCM-155](#)
[PCM-170](#)