

Item # 711-0190 115VAC/60Hz, 2.05 inch Sq., Flush mount, screw termination



115VAC/60Hz, 2.05 inch Sq., Flush mount, screw termination

These 7 figures, AC hour meters with running indicators, offer crisp, distinctive styling for many panel applications. Available in square and round bezel, flush mount or three-hole round panel mount. Each is light-weight, low power, and carry UL, CSA and CE approvals.

Specifications

Model No.	711
Mounting	Panel (mounting hardware included)- Flush Mount
Reset	Non-reset
Termination	1/4 inch (6.3mm) spade terminals with removable screws.
Display	7 figures, 0.14 inch high (3.6mm), 99999.99 hours
Display Height	0.14 Inch
Display Height	3.6 mm
No. of Digits	7
Records	99999.99 hours
Input Voltage	115 VAC 60 Hz \pm 10%
Power	3 watts
Operating Temperature	-22 to +158 °F
Operating Temperature	-30 to +70 °C
Weight	2 oz
Weight	57 gm
Panel Cutout	1.81 Sq. Inch 1.99 Dia. Inch
Panel Cutout	46 Sq. mm 50 Dia. mm
Approvals	UL Recognized and CSA Certified. CE Approved
Stock Availability	Yes



Description

These 7 figure, AC or DC hour meters with running indicators, offer crisp, distinctive styling for many panel applications. Available in square and round bezel, flush mount, or three-hole round panel mount. Each is light-weight, low power, and carry UL, CSA and CE approvals.

Features

- 7 figure, 99999.99
- Various voltage inputs
- Distinctive styling

Options

- Terminations
- Din rail
- Voltages

Specifications

Figures: 7 figures, 0.14" high [3.6mm], 99,999.99 hours
Reset: Non-reset
Voltages: 24, 115, or 230VAC (+/-10%), 50 or 60Hz., 10-80 VDC
Power: 3 watts (AC), 1.2 watt maximum (DC)
Terminations: 1/4" [6.3mm] spade terminals, with removable screws, or 8" [203mm] wire leads

Mounting: Panel (mounting hardware included)
Front Panel: IP65
Temp. Range: -22°F to +158°F [-30°C to +70°C]
Approvals: UL Recognized and CSA Certified (AC only), CE Compliant
Weight: 1.6 oz. [46g]

Models

Description

711-0150 115VAC/60Hz, 2.28" Dia., Flush mount, screw termination
711-0152 230VAC/60Hz, 2.28" Dia., Flush mount, screw termination
711-0160 115VAC/60Hz, 2.93" Dia., 3-hole round, screw termination
711-0162 230VAC/60Hz, 2.93" Dia., 3-hole round, screw termination
711-0163 230VAC/50Hz, 2.93" Dia., 3-hole round, screw termination
711-0164 24VAC/60Hz, 2.93" Dia., 3-hole round, screw termination
711-0171 115VAC/60Hz, 2.93" Dia., 3-hole round, 8" wire leads
711-0180 115VAC/60Hz, 1.89" Sq., Flush mount, screw termination

Models


Description

711-0182 24VAC/60Hz, 1.89" Sq., Flush mount, screw termination
711-0190 115VAC/60Hz, 2.05" Sq., Flush mount, screw termination
711-0192 24VAC/60Hz, 2.05" Sq., Flush mount, screw termination
711-0193 115VAC/50Hz, 2.05" Sq., Flush mount, screw termination
711-0195 24VAC/50Hz, 2.05" Sq., Flush mount, screw termination
731-0046 10-80VDC, 2.93" Dia., 3-hole round, screw termination

* Items in bold are normally in factory stock.


Dimensions

2.28" Dia. Flush




Panel cutout: 1.99" [50] Dia. or 1.81" [46]

3 - Hole Round



Panel cutout: 1.99" [50] Dia. or 1.81" [46] Sq.
 Screws provided: 4-40 x 5/8" [16]
 Bolt hole circle: 2.44" [62]

1.89" or 2.05" Square



Panel cutout: 1.99" [50] Dia. or 1.81" [46] Sq.
 (for 1.89" Sq. use 1.81" [46] Sq. cutout only)

Applications

Medical equipment



Test equipment



Office equipment

