


8 WAY-0° 10 kHz to 1000 MHz

SURFACE MOUNT



JCP8-8



PSC-8



PSC-8A

MODEL NO.	FREQ. RANGE MHz f_L - f_U	ISOLATION dB						INSERTION LOSS, dB Above 9dB						PHASE UNBALANCE Degrees			AMPLITUDE UNBALANCE dB			CASE STYLE Note B	CONNECTION	PRICE \$ Qty. (1-9)
		L	M°	U	L	M°	U	L	M°	U	L	M°	U	L	M°	U	L	M°	U			
NEW ◆ JCP8-8-10	5-1000	34	20	22	16	20	15	0.5	1.5	1.2	2.2	1.8	3.0	5	10	15	1.0	0.7	1.3	BG291	hn	39.95
◆ JCP8-8-10-75	5-1000	34	20	25	15	20	13	0.8	1.5	1.0	2.5	1.8	3.0	3	8	10	0.4	0.5	1.3	BG291	hn	71.95
◆ JCP8-8-850-75	10-850	34	20	25	15	20	15	0.7	1.5	1.0	2.0	1.8	3.0	—	—	—	0.6	0.7	1.0	BG291	hn	69.95
◆ JCP8-8-850	10-850	34	20	25	17	20	15	0.8	1.5	1.0	2.5	1.8	3.0	5	10	15	0.6	0.7	1.0	BG291	hn	69.95
PSC-8-1	0.5-175	30	25	30	20	25	18	0.8	1.2	0.8	1.2	1.0	1.6	1.0	2.5	5.0	0.2	0.3	0.5	C07	bp	74.95
PSC-8-1W	10-600	25	20	23	16	20	16	1.0	1.8	1.2	2.2	1.7	2.8	2.0	4.0	10.0	0.3	0.6	0.9	C07	bp	109.95
■ PSC-8-1-75	0.5-175	25	20	30	20	25	20	0.5	1.0	0.6	1.1	0.7	1.3	1.0	2.5	5.0	0.2	0.2	0.3	C07	bp	78.95
✦ PSC-8-6	0.01-10	40	20	40	25	28	23	0.3	1.0	0.5	1.0	0.6	1.1	4.0	2.5	4.0	0.4	0.2	0.3	C07	bp	93.95
PSC-8A-4	5-500	25	20	23	18	20	15	0.7	1.2	1.0	1.8	1.4	2.5	3.0	8.0	16.0	0.2	0.3	0.5	E10	bq	103.95
■ PSC-8A4-75	1-300	26	20	30	25	30	23	0.8	1.2	0.7	1.1	0.9	1.3	1.0	3.0	8.0	0.2	0.2	0.4	E10	br	93.95

L = low range [f_L to 10 f_L]

M = mid range [10 f_L to $f_U/2$]


U = upper range [$f_U/2$ to f_U]

NOTES:

- ◆ Aqueous washable
- Non-hermetic
- * VSWR, input 1.06:1 typical, 1.2:1 max; output 1.17:1 typical, 1.35:1 max
- ** VSWR, input 1.22:1 typical, 1.5:1 max; output 1.11:1 typical, 1.30:1 max
- *** VSWR, input 1.25:1 typical, 1.8:1 max; output 1.10:1 typical 1.40:1 max
- ✦ Below 0.1 MHz power handling decrease as to typically 15 dBm at 0.01 MHz, 23 dBm at 0.025 MHz, and 29 dBm at 0.05 MHz.
- Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.
- ⊗ When specification for only M range given, specification applies to entire frequency range.
- ▲ Available only with SMA connectors.
- A. General Quality Control Procedures, Environmental Specifications, Hi-Rel and MIL description are given in General Information (Section 0).
- B. Connector types and case mounted options, case finishes are given in section 0, see "Case styles & Outline Drawings".
- C. Prices and specifications subject to change without notice.
- 1. Absolute maximum power, voltage and current ratings:
 - 1a. Matched power rating,
 - Models ZB8PD, ZC8PD 10 Watt
 - Model JCP8-8-10 0.5 Watt
 - All other models, 1 Watt
 - 1b. Internal load dissipation,
 - Model ZC8PD1 2 Watt
 - Models JCP8-8-850/75, JCP8-8-10 0.875 Watt
 - ZB8PD, ZC8PD 0.875 Watt
 - All other models, 0.62 Watt

Surface Mount □, Plug-In & Coaxial

500 kHz to 8.4 GHz



MODEL NO.	FREQ. RANGE MHz f_L - f_U	ISOLATION dB			INSERTION LOSS, dB Above 9dB						PHASE UNBALANCE Degrees			AMPLITUDE UNBALANCE dB			CASE STYLE Note B	CONNECTION	PRICE \$ Qty. (1-9)
		L Typ. Min.	M° Typ. Min.	U Typ. Min.	L Typ.	M° Max.	U Typ.	L Max.	M° Typ. Max.	U Typ. Max.	L Max.	M° Max.	U Max.	L Max.	M° Max.	U Max.			
NEW ZC8PD-900*	800-900		30	20				0.4	0.7			5.0		0.4			AB186	—	158.95
ZC8PD1-10	300-1000		27	17				0.6	1.4			8.0		0.7			DE749	—	169.95
ZCSC-8-1	2-250	37	27	30	20	24	18	0.65	1.2	0.8	1.2	1.0	1.6	2.0	4.0	8.0	UU215	—	119.95
ZFSC-8-1	0.5-175	30	25	30	20	25	18	0.8	1.2	0.8	1.2	1.0	1.6	1.0	2.5	5.0	R29	—	99.95
■ ZFSC-8-1-75	0.5-175	25	20	30	20	25	20	0.5	1.0	0.6	1.1	0.7	1.3	1.0	2.5	5.0	R29	—	102.95
■ ZFSC-8-4-75	5-1000	35	20	25	16	20	15	0.4	1.0	0.6	1.6	1.6	2.7	2.0	7.0	13.0	R29	—	139.95
■ ZFSC-84-75	1-300	26	20	30	25	30	23	0.8	1.5	0.7	1.1	0.9	1.5	4.0	3.0	8.0	R29	—	119.95
■ ZFSC-8375	50-90	30	25	30	25	25	25	1.0	1.0	1.0	1.3	1.3	1.3	2.0	2.0	2.0	R29	—	119.95
ZFSC-8-4	5-700	35	20	25	17	20	17	0.8	1.2	1.2	1.8	1.8	2.5	2.0	5.0	15.0	R29	—	128.95
ZFSC-8-43	10-1000	23	20	25	20	26	20	1.0	1.6	1.4	2.1	2.1	2.9	5.0	10.0	20.0	R29	—	138.95
ZB8PD-1**	800-960		30	20				0.4	0.9			8.0		0.4			Z41	—	138.95
ZB8PD-2	1000-2000		24	17				0.8	1.3			18.0		0.8			Z41	—	138.95
ZB8PD-4	2000-4200		23	16				0.8	1.8			10.0		1.2			Z41	—	138.95
▲ ZB8PD-6.4	5600-6800		26	18				0.8	1.7			15.0		0.7			Z41	—	138.95
ZB8PD-8.4	7200-8400		25	20				0.9	1.6			15.0		0.8			Z41	—	149.95
ZB8PD-2000***	800-2000		26	18				0.8	1.7			—		0.7			Z41	—	149.95
■ ZB8PD-22-75	950-2200		24	16				0.7	1.6			—		0.7			Z41	—	189.95

L = low range [f_L to $10 f_L$]

M = mid range [$10 f_L$ to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

NSN GUIDE MCL NO.

NSN	
6625-01-365-5615	PSC-8-1
5985-01-482-9739	ZB8PD-1(N)
5985-01-372-8880	ZB8PD-4(SMA)
5820-01-136-7244	ZFSC-8-1(BNC)
6620-01-223-1235	ZFSC-8-1(SMA)
5895-01-326-8664	ZFSC-8-1-75
6625-01-333-1125	ZFSC-8-43(SMA)
5895-01-229-0156	ZFSC-8375

pin connections see case style outline drawings

PORT	SUM	#1	#2	#3	#4	#5	#6	#7	#8	NOT USED	GND EXT.	CASE GND
bp	2	1	5	9	13	16	12	8	4	10,11	3,6,7,14,15	3,6,7,14,15
bq	29	7	16	31	24	9	2	26	17	4,5,15	—	All other pins
br	29	7	16	31	24	9	2	26	17	15	—	All other pins
hn	1	3	4	5	6	9	10	11	12	—	2,7,8,13,14	2,7,8,13,14