

Description:

The CVH Series of transient surge suppressors is an extended version of CV Series of disc-shaped varistors. The CVH Series consists of 7 mm, 10 mm, 14 mm, 20 mm and 23 mm sized varistors of extremely high current and energy capabilities.

They provide the increased level of protection necessary for the transients expected in telecommunication and AC power networks. AC operating voltage of these varistors ranges from 60V to 680V.



Features:

- AC operating voltage (Vrms) from 60V to 680V
- DC operating voltage (Vdc) from 85V to 895V
- Broad range of current and energy handling capability
- +85°C continuous operating temperature
- 5 model sizes available from 7mm to 23mm
- Sizes 7mm, 10mm, 14mm, 20mm
- UL, CSA, CECC approved

General Technical Data		
Climatic Category	40 / 85 / 56	In accordance with IEC 60068-1
Operating Temperature	-40°C to +85°C	In accordance with CECC 42 000
Storage Temperature Range	-40°C to +125°C	
Threshold Voltage Temperature Coefficient	≤0.05% / °C	
Isolation Voltage Capability	> 2.5kV	In accordance with CECC 42 000
Response Time	< 25 ns	
Insulation Resistance	> 1 Gohm	In accordance with CECC 42 000

How to Order


	1	2	3	4	5	6	7	8	9	10	
	C	V	H	1	4	0	K	1	4	B	
Product Series	Vrms voltage	Tolerance	Disc Diameter	Packaging	Specials						
						Code	Description	Code	Description		
						B	Bulk	-XX	Special		
						T	Tape and Reel				
						A	Ammo				
CVH		Size (mm)									
		Code	Tol								
		K	10%	07							
		L	15%	10							
		M	20%	14							
		S	Special	20							
				23							

Legacy Part Number before January 3rd, 2010

SEI Type		Lead Style		Vrms	Tolerance		Disc Diameter	Packaging		Specials
CV+		1		140	K		14	B		XX
Type	Description	Lead Style	Description			Code	Tolerance	Size (mm)	Code	Description
CV+	Medium Voltage Leaded Varistor	1	Straight			K	10%	07	B	Bulk
						L	15%	10	R	Tape and Reel
						M	20%	14	A	Ammo
						S	Special	20		
								23		

Standard Packaging Options / Quantities

Series	Range (Vrms)	Disc Diameter								
		7mm		10mm		14mm		20mm		23mm
		Reel	Bulk	Reel	Bulk	Reel	Bulk	Reel	Bulk	Bulk
CVH	60 - 75	1,500	1,500	1,300	600	700	500	600	300	N/A
	95	1,500	1,000	1,300	600	600	500	600	300	N/A
	115 - 130	1,300	1,000	1,000	500	600	500	500	300	250
	140 - 150	1,200	1,000	1,000	500	600	500	500	300	250
	175	1,200	1,000	1,000	500	500	500	500	300	250
	230	1,000	1,000	1,000	500	500	300	400	300	150
	250 - 275	1,000	1,000	800	500	400	300	400	300	150
	300	900	1,000	800	500	400	300	400	200	150
	320	N/A	N/A	800	500	400	300	300	200	150
	385	N/A	N/A	700	400	400	300	300	200	150
	420	N/A	N/A	700	400	300	300	300	200	150
	460 - 550	N/A	N/A	600	400	300	300	300	200	150
	625	N/A	N/A	600	400	300	300	250	200	150



Device Ratings and Dimensions

Part Number	V_{RMS} (volts)	V_{DC} (volts)	V_{N} (volts)	V_{C} (volts)	I_{C} (amps)	W_{MAX} (joules)	P_{MAX} (watts)	I_{P} (amps)	C_{TYP} (pF)	D_{MAX} (mm)	t_{MAX} (mm)	R (mm)	d (mm)	h_{MAX} (mm)
CVH60K07	60	85	100	165	10	9	0.25	1,750	680	9	3.5	5	0.6	11.5
CVH60K10	60	85	100	165	25	18	0.4	3,500	1,200	12.5	4.1	7.5	0.8	15
CVH60K14	60	85	100	165	50	38	0.6	6,000	2,200	16.5	4.2	7.5	0.8	20
CVH60K20	60	85	100	165	100	77	1	12,000	4,100	22.5	4.6	10	1	26
CVH75K07	75	100	120	200	10	11	0.25	1,750	550	9	3.6	5	0.6	11.5
CVH75K10	75	100	120	200	25	24	0.4	3,500	950	12.5	4.2	7.5	0.8	15
CVH75K14	75	100	120	200	50	46	0.6	6,000	1,800	16.5	4.2	7.5	0.8	20
CVH75K20	75	100	120	200	100	88	1	12,000	3,300	22.5	4.6	10	1	26
CVH95K07	95	125	150	250	10	14	0.25	1,750	440	9	3.8	5	0.6	11.5
CVH95K10	95	125	150	250	25	28	0.4	3,500	750	12.5	4.3	7.5	0.8	15
CVH95K14	95	125	150	250	50	58	0.6	6,000	1,400	16.5	4.3	7.5	0.8	20
CVH95K20	95	125	150	250	100	116	1	12,000	2,600	22.5	4.6	10	1	26
CVH115K07	115	150	180	300	10	16	0.25	1,750	360	9	4	5	0.6	11.5
CVH115K10	115	150	180	300	25	34	0.4	3,500	650	12.5	4.3	7.5	0.8	15
CVH115K14	115	150	180	300	50	71	0.6	6,000	1,200	16.5	4.4	7.5	0.8	20
CVH115K20	115	150	180	300	100	128	1	12,000	2,100	22.5	4.8	10	1	26
CVH130K07	130	170	205	340	10	19	0.25	1,750	360	9	4	5	0.6	11.5
CVH130K10	130	170	205	340	25	38	0.4	3,500	580	12.5	4.5	7.5	0.8	15
CVH130K14	130	170	205	340	50	77	0.6	6,000	1,050	16.5	4.6	7.5	0.8	20
CVH130K20	130	170	205	340	100	154	1	12,000	1,900	22.5	5	10	1	26
CVH130K23	130	170	205	340	100	172	1	15,000	3,500	25	5	10	1	27
CVH140K07	140	180	220	360	10	22	0.25	1,750	300	9	4.1	5	0.6	11.5
CVH140K10	140	180	220	360	25	42	0.4	3,500	540	12.5	4.6	7.5	0.8	15
CVH140K14	140	180	220	360	50	85	0.6	6,000	980	16.5	4.7	7.5	0.8	20
CVH140K20	140	180	220	360	100	170	1	12,000	1,800	22.5	5.1	10	1	26
CVH140K23	140	180	220	360	100	190	1	15,000	3,200	25	5.1	10	1	27
CVH150K07	150	200	240	395	10	23	0.25	1,750	280	9	4.3	5	0.6	11.5
CVH150K10	150	200	240	395	25	46	0.4	3,500	510	12.5	4.6	7.5	0.8	15
CVH150K14	150	200	240	395	50	92	0.6	6,000	900	16.5	4.8	7.5	0.8	20
CVH150K20	150	200	240	395	100	185	1	12,000	1,600	22.5	5.2	10	1	26
CVH150K23	150	200	240	395	100	207	1	15,000	2,900	25	5.2	10	1	27
CVH175K07	175	225	270	455	10	26	0.25	1,750	250	9	4.8	5	0.6	11.5
CVH175K10	175	225	270	455	25	53	0.4	3,500	440	12.5	4.9	7.5	0.8	15
CVH175K14	175	225	270	455	50	108	0.6	6,000	800	16.5	4.9	7.5	0.8	20
CVH175K20	175	225	270	455	100	210	1	12,000	1,400	22.5	5.3	10	1	26
CVH175K23	175	225	270	455	100	235	1	15,000	2,500	25	5.3	10	1	27
CVH230K07	230	300	360	595	10	35	0.25	1,750	190	9	4.8	5	0.6	11.5
CVH230K10	230	300	360	595	25	71	0.4	3,500	350	12.5	5.4	7.5	0.8	15
CVH230K14	230	300	360	595	50	143	0.6	6,000	620	16.5	5.5	7.5	0.8	20
CVH230K20	230	300	360	595	100	280	1	12,000	1,100	22.5	5.9	10	1	26
CVH230K23	230	300	360	595	100	313	1	15,000	2,200	25	5.9	10	1	27

Device Ratings and Dimensions

Part Number	V _{RMS} (volts)	V _{DC} (volts)	V _N (volts)	V _C (volts)	I _C (amps)	W _{MAX} (joules)	P _{MAX} (watts)	I _P (amps)	C _{TYP} (pF)	D _{MAX} (mm)	t _{MAX} (mm)	R (mm)	d (mm)	h _{MAX} (mm)
CVH250K07	250	320	390	650	10	38	0.25	1,750	180	9	5	5	0.6	11.5
CVH250K10	250	320	390	650	25	77	0.4	3,500	320	12.5	5.6	7.5	0.8	15
CVH250K14	250	320	390	650	50	154	0.6	6,000	580	16.5	5.7	7.5	0.8	20
CVH250K20	250	320	390	650	100	300	1	12,000	1,000	22.5	6.1	10	1	26
CVH250K23	250	320	390	650	100	336	1	15,000	1,900	25	6.1	10	1	27
CVH275K07	275	350	430	710	10	44	0.25	1,750	160	9	5.6	5	0.6	11.5
CVH275K10	275	350	430	710	25	88	0.4	3,500	300	12.5	5.8	7.5	0.8	15
CVH275K14	275	350	430	710	50	170	0.6	6,000	530	16.5	5.9	7.5	0.8	20
CVH275K20	275	350	430	710	100	330	1	12,000	900	22.5	6.3	10	1	26
CVH275K23	275	350	430	710	100	370	1	15,000	1,600	25	6.3	10	1	27
CVH300K07	300	385	470	775	10	46	0.25	1,750	150	9	5.8	5	0.6	11.5
CVH300K10	300	385	470	775	25	93	0.4	3,500	280	12.5	6.1	7.5	0.8	15
CVH300K14	300	385	470	775	50	192	0.6	6,000	490	16.5	6.1	7.5	0.8	20
CVH300K20	300	385	470	775	100	380	1	12,000	850	22.5	6.6	10	1	27
CVH300K23	300	385	470	775	100	426	1	15,000	1,300	25	6.6	10	1	29
CVH320K10	320	420	510	840	25	104	0.4	3,500	260	12.5	5.9	7.5	0.8	16
CVH320K14	320	420	510	840	50	209	0.6	6,000	460	16.5	6.5	7.5	0.8	21
CVH320K20	320	420	510	840	100	420	1	12,000	800	22.5	6.8	10	1	27
CVH320K23	320	420	510	840	100	470	1	15,000	1,100	25	6.8	10	1	29
CVH385K10	385	505	620	1025	25	106	0.4	3,500	230	12.5	6.4	7.5	0.8	16
CVH385K14	385	505	620	1025	50	219	0.6	6,000	390	16.5	6.9	7.5	0.8	21
CVH385K20	385	505	620	1025	100	430	1	12,000	650	22.5	7.5	10	1	27
CVH385K23	385	505	620	1025	100	480	1	15,000	1,000	25	7.5	10	1	29
CVH420K10	420	560	680	1120	25	110	0.4	3,500	210	12.5	7.3	7.5	0.8	16
CVH420K14	420	560	680	1120	50	230	0.6	6,000	370	16.5	7.4	7.5	0.8	21
CVH420K20	420	560	680	1120	100	460	1	12,000	620	22.5	7.8	10	1	27
CVH420K23	420	560	680	1120	100	515	1	15,000	950	25	7.8	10	1	29
CVH460K10	460	615	750	1240	25	120	0.4	3,500	200	12.5	7.8	7.5	0.8	16
CVH460K14	460	615	750	1240	50	250	0.6	6,000	340	16.5	7.8	7.5	0.8	21
CVH460K20	460	615	750	1240	100	500	1	12,000	560	22.5	8.2	10	1	27
CVH460K23	460	615	750	1240	100	560	1	15,000	900	25	8.2	10	1	29
CVH510K10	510	670	820	1355	25	131	0.4	3,500	180	12.5	8.2	7.5	0.8	16
CVH510K14	510	670	820	1355	50	258	0.6	6,000	310	16.5	8.2	7.5	0.8	21
CVH510K20	510	670	820	1355	100	520	1	12,000	510	22.5	8.7	10	1	27
CVH510K23	510	670	820	1355	100	582	1	15,000	650	25	8.7	10	1	29
CVH550K10	550	745	910	1500	25	153	0.4	3,500	170	12.5	8.8	7.5	0.8	16
CVH550K14	550	745	910	1500	50	300	0.6	6,000	290	16.5	8.8	7.5	0.8	21
CVH550K20	550	745	910	1500	100	560	1	12,000	480	22.5	9.2	10	1	27
CVH550K23	550	745	910	1500	100	627	1	15,000	800	25	9.2	10	1	29
CVH575K10	575	750	950	1570	25	155	0.4	3,500	165	12.5	8.9	7.5	0.8	16
CVH575K14	575	750	950	1570	50	305	0.6	6,000	280	16.5	8.9	7.5	0.8	21
CVH575K20	575	750	950	1570	100	585	1	12,000	460	22.5	9.4	10	1	27
CVH575K23	575	750	950	1570	100	650	1	15,000	720	25	9.4	10	1	29
CVH625K10	625	825	1000	1650	25	159	0.4	3,500	160	12.5	9.1	7.5	0.8	16
CVH625K14	625	825	1000	1650	50	315	0.6	6,000	270	16.5	9.2	7.5	0.8	21
CVH625K20	625	825	1000	1650	100	640	1	12,000	420	22.5	9.7	10	1	27
CVH625K23	625	825	1000	1650	100	690	1	15,000	680	25	9.7	10	1	29
CVH680K10	680	895	1100	1815	25	171	0.4	3,500	150	12.5	9.7	7.5	0.8	16
CVH680K14	680	895	1100	1815	50	340	0.6	6,000	250	16.5	9.8	7.5	0.8	21
CVH680K20	680	895	1100	1815	100	690	1	12,000	390	22.5	10.2	10	1	27
CVH680K23	680	895	1100	1815	100	745	1	15,000	620	25	10.2	10	1	29