

14 Series


RoHS
Compliant

NYLON 6.6

GENERAL PURPOSE



MATERIAL OPERATING TEMPERATURE: -40°C to +85°C

APPLICATION OPERATING TEMPERATURE: -10°C to +85°C



Part Number	Ball Diameter mm [Inch]	Length mm [Inch]	Max Bundle Diameter mm [Inch]	Min Loop Tensile Kg [lb]
S - 50lb				
14-S210	4.5 [.177]	210 [8.0]	53.5 [2.10]	22 [50]
14-S310	4.5 [.177]	310 [12.0]	83.8 [3.30]	22 [50]
HD - 120lb				
14-HD460	6.5 [.255]	460 [18.0]	129.5 [5.10]	55 [120]
14-HD610	6.5 [.255]	610 [24.0]	175.2 [6.90]	55 [120]

PART NUMBER SYSTEM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[14-HD460B-C](#) [14-HD610N-C](#) [14-HD460N-C](#) [14-HD610B-C](#) [14-S210B-C](#) [14-S210N-C](#) [14-S310B-C](#) [14-S310N-C](#)