

Search within category

GO

BUY NOW

DESIGN / INSTALL



GPQC15-1/0

Access floor grounding clamp for 1 1/2" round pedestals.

Specs		Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
CSA Certified		Meets CSA 22.2 No. 41-13Y			
Standards		TIA-607-B			
UL Listed		UL 467			
Round Pedestal (In.)		1 1/2			
Round Pedestal (mm)		38.1			
Square Pedestal (In.)		—			
MCBN Conductor Size Range (AWG)		#6 SOL - 1/0 STR			
MCBN Conductor Size Range (mm²)		16 - 50			
Depth (In.)		4.47			
Depth (mm)		113.5			
Height (In.)		3.19			
Height (mm)		81.0			
Width (In.)		3.44			
Width (mm)		87.4			
Tightening Torque Clamp		150 In. - Lbs.			
Tightening Torque Conductor		385 In. - Lbs.			
Material		Electolytic Bronze/Zinc Plated			
Part Features		Designed to bond perpendicular MCBN conductors, Bonds to pedestal with a single bolt to simplify installation.			
RoHS Compliancy Status		Compliant			
Min. Order Qty.		1			