

Item no.:	769-125
Product description:	2-CONDUCTOR FEMALE PLUG to be fixed on receptacle terminal blocks or male connectors WITH CODING FINGERS COMMONING POSSIBILITY WITH ADJACENT JUMPERS AND STAGGERED JUMPERS 5 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 20 pieces

RoHS compliant

Product group	18 (X-COM-SYSTEM)
pole count	5
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	25.072 g
Color	gray
Wiring type	Front-entry
No. of connection Points	10
No. of potentials	5
Height	45.2 mm
Height	1.78 in
Width	25 mm

Width	0.98 in
Depth	35.9 mm
Depth	1.413 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
769-125	ABS	05-HG476175/3-PDA	500	32	4
769-125	CSA	154112-1101144	300	20	28-12
769-125	KEMA	2077750.01	500	32	4
769-125	UR	E45171	600	20	16-12
769-125	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected