


REV.	ECN. NO.	APPD.
BX1	TBD	Simon Chen



WIRE TABLE

J1	CONNECTION	J2	REMARK
	COLOR		
1	RED	1	VBUS
2	WHITE	2	D-
3	GREEN	3	D+
4	BLACK	4	GND
5	BLUE	5	STP1-
6	YELLOW	6	STP1+
7	DRAIN	7	GND
8	PURPLE	8	STP2-
9	ORANGE	9	STP2+
SHELL	BRAID	SHELL	

RAW CABLE SPEC.

ITEM	RAW CABLE P/N	SDPAWG	UTPAWG	PowerAWG	OD mm	Color
1	791-1017-035	30	30	24	Ø4.8	DARK GREY

FOXCONN CONFIDENTIAL

9	USB 3.0 B PLUG CONN.	1	UC2090C-K05-4F	HOUSING: PBT, COLOR BLUE. CONTACT: Au 30".
8	USB 3.0 B PLUG FRONT SHELL	1	024-0001-1096	100u" Min. Ni OVER THE SURFACE
7	USB 3.0 B PLUG REAR SHELL	1	024-0001-1095	NI AND SN PLATING
6	USB 3.0 B PLUG OVER MOLD	A/R	901-C301-024	UL 94V-0, PVC DARK GREY
5	RAW CABLE	A/R	791-1017-035	SHOW AS Tab2. RAW CABLE SPEC.
4	USB 3.0 A PLUG OVER MOLD	A/R	901-C301-024	UL 94V-0, PVC DARK GREY
3	USB 3.0 A PLUG CONN.	1	075-0001-238	CONTACT: Au 30".
2	USB 3.0 A PLUG REAR SHELL	1	024-0001-8881	SPCC T=0.3MM
1	USB 3.0 A PLUG FRONT SHELL	1	024-0001-8880	SPCC T=0.3MM

NO	DESCRIPTION	Q'TY	P/N	REMARK
X.±	X°.±	UNITS	mm	NAME<INTENDED USE>
.X± 0.2	.X°.±	MAT'L		CUSTOMER DRAWING
.XX±	.XX°.±			PART NO.<INTENDED USE>
.XXX±	.XXX°.±	FINISH		CUED002F-K18-OF
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.				APPD: Simon Chen 02/06/11
				CHKD: Xianbao Su 02/06/11
				DR: Xianhui Lei 02/06/11
				DWG NO: 605-*
				SCALE SHEET REV.
				NONE 1/1 BX1

NOTES:

- DIM. MARKED TO BE CHECKED.
- ANY OPEN,MISSWIRING&SHORTARE NOT PERMITTED, PRODUCT 100% TEST.
- INSULATION RESISTANCE: 100M OHM(MIN)/300VDC, CONTACT RESISTANCE: 2.0 OHMS(MAX)
- HARMFUL MATERIAL CONTROL PLEASE FOLLOW Doc.No."EPI12".