

Models 1794, 1795 & 1796

Regulated DC Power Supplies

Data Sheet

Models 1794, 1795 & 1796

Regulated DC Power Supplies

Models 1794, 1795 & 1796 are cost effective, high power, regulated DC power supplies. These linear power supplies are high power workhorses that will easily deliver clean power to your high-current circuits. Special features include the ability to set constant current with no load and remote sense to compensate for any wire loss.

The power supplies are designed to have superior performance to comparable models costing 20 to 30% more. Meets CE specifications.

- **Constant Voltage/Constant Current Operation**
- **Remote Programming Facility**
- **Facility for Presetting the Output Voltage and Max. Load Current Limits**
- **Separate DC Output ON/OFF Switch**
- **Remote Sensing Facility**
- **High Stability and Close Regulation $\pm 0.01\%$**
- **Meet CE Specifications**



Specifications		models		
	1794	1795	1796	
Output (DC)	0-32V	0-64V	0-16V	
Output Current (DC)	0-30A	0-15A	0-50A	
Constant Voltage Mode				
Line Regulation	$\pm 0.01\% \pm 2\text{mV}$			
Load Regulation	$\pm 0.01\% \pm 2\text{mV}$			
Ripple and Noise	1mV rms max (20Hz - 20MHz)			
Constant Current Mode				
Line Regulation	$\pm 0.05\% \pm 10\text{mA}$			
Load Regulation	$\pm 0.05\% \pm 10\text{mA}$			
Ripple and Noise	6mA rms Max (20Hz - 20MHz)			
Overload Protection	Constant current type			
Stability	$\pm 0.2\% \pm 10\text{mV}$ in CV mode $\pm 0.5\% \pm 10\text{mA}$ in CC mode			
Operating Temperature	32° to 104°F (0° to 40°C)			
Input	115V / 60 Hz			
Dimension (W x H x D)	19 x 5.25 x 15.75" (483 x 133 x 400mm)			
Accessories Supplied	User Manual			

B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887
Tel: 714-921-9095, Fax: 714-921-6422
www.bkprecision.com

Specifications subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1795](#)