

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING
BZ-RW842

CATALOG LISTING
BZ-RW842
PAGE 1 OF 1

M

ISSUE
11

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO17272	L M H	5 SEP 62
B	CO30626	D B W	24 MAY 72
C	CO46304	J A P	12 OCT 79
D	CO58037	CO	5 OCT 99
E	SMA 78874	1 OCT 85	
F	DLT 94212-J	18 NOV 94	
G	203222	5 OCT 99	
	CSL 6 JUN 01		

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTES

- △ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS.
- 2 - FORCES ARE CHECKED WITH SWITCH LYING ON SIDE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO; THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — 5 GRAM MAX
RELEASE FORCE — — — 1 GRAM MIN
DIFFERENTIAL TRAVEL — — .004 — .020
OVERTRAVEL — — — — .141 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L95
10A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC

L288



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .060 LB

RASTER

FO-80378

DRAWN

LMH

SEP 62