






REV.	DATE	ECR NO.	DESCRIPTION
NC	04/22/07	—	INITIAL RELEASE
A	10/15/08	—	REVISE 174/U TO 179/U CABLE CALL OUT.



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .178" [4.52]
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068" [1.73]

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	10/15/08						
7						CHECKED								
6						ISSUED				PART DESCRIPTION TNC CRIMP PLUG (FOR RG–179/U, 187/U, B9221 CABLE)				
5	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1							
4	SLEEVE	DELIRIN	NATURAL	1		PART NO. 122117								
3	INSULATOR	DELIRIN	NATURAL	1										
2	CONTACT PIN	BRASS	GOLD	1										
1	SHELL/BODY	BRASS	NICKEL	1		DWG. NO. 122117.DWG					REV. A	SIZE A	SCALE NA	
	DESCRIPTION	MATERIAL	FINISH	QTY										